

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [45570-3000](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: 3.96mm (.156") Pitch MarKK™ Crimp Terminal, 18 to 20 AWG, Pre-Tinned Plating, Chain and Reel

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-45570-001 \(PDF\)](#)
[Product Specification PS-45570-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	45570
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnection System
Product Name	KK®, MarKK™
UPC	756054764909

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.242/g
Packaging Type	Reel
Plating min - Mating	2.032µm
Plating min - Termination	2.032µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.12mm
Wire Size AWG	18, 20
Wire Size mm²	1.14

Electrical

Current - Maximum per Contact	13A
Voltage - Maximum	600V DC

Material Info

Reference - Drawing Numbers

Product Specification	PS-45570-001
Sales Drawing	SD-45570-001
Test Summary	TS-45570-001



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[45570Series](#)

Mates With

3.96mm KK™ Headers . [41661](#) , [41662](#) , [41671](#) , [41672](#) , [41681](#) . [41682](#) , [41771](#) , [41772](#) , [41971](#) , [41792](#)

Use With

KK™ Crimp Terminal Housings, [41695](#) , [6442](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030016
Hand Tool for 3.96mm Crimp	0638193600

Terminals, 18-20 AWG Wire T2 Terminator	<u>0638562000</u>
Tooling Die for 3.96mm Center Terminals, 18-20 AWG Wire FineAdjust™	<u>0638662000</u>
Applicator for 3.96mm Centers Female Terminals	

This document was generated on 09/19/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION