



PRODUCT BRIEF

EPCOS Sensors

SMD NTC Thermistors for LED Applications

Kit: B57999V3999J099	Data Sheet Link	R ₂₅ Ω	R ₂₅ Tolerance	No. of R/T Characteristic	B _{25/50} K	B _{25/85} K	B _{25/100} K	Case Size
Kit Contents:								
B57221V2103J060	DataSheet	10K	±5%	8502	3940	3980	4000 ±3%	0402
B57221V2473J060	DataSheet	47K	±5%	8502	3940	3980	4000 ±3%	0402
B57230V2103F260	DataSheet	10K	±1%	8509	3380	3435	3455 ±1%	0402
B57232V5103F360	DataSheet	10K	±1%	8509	3380	3435	3455 ±1%	0402
B57232V5103J360	DataSheet	10K	±5%	8509	3380	3435	3455 ±1%	0402
B57251V5103J060	DataSheet	10K	±5%	8502	3940	3980	4000 ±3%	0402
B57261V2223J060	DataSheet	22K	±5%	8506	4473	4548	4575 ±3%	0402
B57321V2103H060	DataSheet	10K	±3%	8502	3940	3980	4000 ±3%	0603
B57321V2103J060	DataSheet	10K	±5%	8502	3940	3980	4000 ±3%	0603
B57330V2103F260	DataSheet	10K	±1%	8509	3380	3435	3455 ±1%	0603
B57330V2103J260	DataSheet	10K	±5%	8509	3380	3435	3455 ±1%	0603
B57332V5103F360	DataSheet	10K	±1%	8509	3380	3435	3455 ±1%	0603
B57332V5103J360	DataSheet	10K	±5%	8509	3380	3435	3455 ±1%	0603
B57352V5103H060	DataSheet	10K	±3%	8507	4386	4455	4480 ±3%	0603
B57352V5103J060	DataSheet	10K	±5%	8507	4386	4455	4480 ±3%	0603
B57352V5104F360	DataSheet	100K	±1%	8507	4386	4455	4480 ±3%	0603
B57352V5104J360	DataSheet	100K	±5%	8507	4386	4455	4480 ±3%	0603
B57352V5223H060	DataSheet	22K	±3%	8507	4386	4455	4480 ±3%	0603
B57352V5223J060	DataSheet	22K	±5%	8507	4386	4455	4480 ±3%	0603
B57352V5473H060	DataSheet	47K	±3%	8507	4386	4455	4480 ±3%	0603
B57352V5473J060	DataSheet	47K	±5%	8507	4386	4455	4480 ±3%	0603
B57371V2223H060	DataSheet	22K	±3%	8507	4386	4455	4480 ±3%	0603
B57371V2223J060	DataSheet	22K	±5%	8507	4386	4455	4480 ±3%	0603
B57371V2473H060	DataSheet	47K	±3%	8507	4386	4455	4480 ±3%	0603
B57371V2473J060	DataSheet	47K	±5%	8507	4386	4455	4480 ±3%	0603
B57371V2474H060	DataSheet	470K	±3%	8507	4386	4455	4480 ±3%	0603

B57371V2474J060	DataSheet	470K	±5%	8507	4386	4455	4480 ±3%	0603
B57374V2104F060	DataSheet	100K	±1%	8507	4386	4455	4480 ±3%	0603
B57374V2104J060	DataSheet	100K	±5%	8507	4386	4455	4480 ±3%	0603

Buy Kit

[View Kit Contents](#)

Learn More About [EPCOS Design Engineering Sample Kits](#)