

Waterproof Speakers

67 Series



IP67 Rated
Dust-tight
Waterproof up to 1m

70% of the Earth's surface is covered with water.

DB's 67 Series Waterproof Speakers keep it out of your product.

DB Unlimited's 67 Series Waterproof Speakers are specifically designed and manufactured to deliver the outstanding performance you expect from DB Unlimited while also providing IP67 protection to your product. The 67 Series survives and continues to operate normally after being exposed to dust, splashes, spills and sprays — even submersion.*

The 67 Series' starting line-up includes 4Ω and 8Ω speakers, ranging from 18mm to 44mm. They come in round, rectangle and oval frames; with and without mounting flanges. Supporting frequencies as low as 300Hz, DB Unlimited's 67 Series speakers are suitable for virtually every audio application requiring water resistance.

Visit www.dbunlimitedco.com to learn more about DB Unlimited's 67 Series Waterproof Speakers.

DB PN	H mm	W mm	L mm	FR Hz	Ω	W
SW181004-1	4	18	18	1050 ~ 10000	4	1
SW200508-1	5.5	20	20	500 ~ 10000	8	1.5
SW200908-1	4.8	20	20	900 ~ 10000	8	1
SW201108-1	3.6	14	20	1100 ~ 10000	8	0.8
SW230704-1	4	23	23	700 ~ 10000	4	1
SW250508-1	6.7	16	25	550 ~ 10000	8	1
SW250808-1	4.7	16	25	850 ~ 10000	8	0.5
SW280408-1	8.3	28	28	400 ~ 10000	8	1.5
SW280408-2	7.8	28	28	400 ~ 10000	8	0.8
SW280708-1	5.5	28	28	700 ~ 10000	8	1.5
SW350608-1	4.6	25	35	600 ~ 10000	8	1.2
SW350804-1	5.8	20	35	850 ~ 20000	4	2
SW360308-1	6.9	36	36	350 ~ 10000	8	2
SW380408-1	6.5	28	38	400 ~ 10000	8	2
SW390608-1	5.5	29.7	39.7	600 ~ 20000	8	1.5
SW400508-1	5.6	40	40	550 ~ 10000	8	0.5
SW400704-1	11.8	28.4	40	750 ~ 10000	4	2
SW401404-1	6.5	20	40	300 ~ 10000	4	2
SW440804-1	8.3	44.6	44.6	800 ~ 10000	4	2.5



SW181004-1 SW200508-1 SW200908-1 SW201108-1



SW230704-1 SW250508-1 SW250808-1 SW280408-1



SW280408-2 SW280708-1 SW350608-1 SW360308-1



SW380408-1



SW400704-1



SW401404-1



SW440804-1

*When mounted appropriately