

PHOENIX CONTACT DIN Rail Mounted Terminal Blocks



DIMENSIONS: mm

A	B	C	D	E	F
<ul style="list-style-type: none"> Width: 17.5mm Fuse Size: 10.3x38 18-4AWG (UL) 30A (UL) 	<ul style="list-style-type: none"> Width: 40mm Fuse Size: 27x60 14-1AWG (UL) 60A (UL) 	<ul style="list-style-type: none"> Width: 8.2mm Fuse Size: 5x20mm, 5x25mm, 5x30mm 26-10AWG (UL) 12A (UL) 	<ul style="list-style-type: none"> Width: 10.2mm Fuse Size: 6.3x32mm 26-8 AWG (UL) 25A (UL) 	<ul style="list-style-type: none"> Width: 18mm Fuse Size: 10.3x38mm 16-4AWG (UL) 30A (UL) 	<ul style="list-style-type: none"> Width: 8.2mm Fuse Size: 5x20mm, 6.3x32mm 24-8AWG (UL) 15A upper/30A lower (UL)

DIN RAIL MOUNTED TERMINAL FUSE BLOCKS

Color: Black • 600V (UL)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Phoenix Part No.	Fig.	Phoenix Type	Description	Price Each			Accessories (See Accessories page for pricing and descriptions)				
					1	10	50	Bridge		Screwdriver	End Bracket	Din Rail Type
						Insertion	Fixed					
Branch Circuit Protection - Class CC and J												
651-3048580	3048580	A	UK 10.3-CC HESI	For Class CC fuses	15.92	15.08	13.87	651-3009299	-	651-1205066	-	NS 35
651-3048616	3048616	A	UK 10.3-CC HESI/LED	For Class CC fuses with LED, 110-600V	26.32	24.93	22.93	651-3009367	-	651-1205066	-	NS 35
Fuse Terminal Blocks with Disconnect Lever												
651-3004100	3004100	B	UK 5 HESI	Fuse Block	10.59	10.18	9.63	651-3118135	-	651-1205053	651-0800886	NS 35
651-3004126	3004126	B	UK 5 HESI/LED 24	Fuse Block with LED, 15-30V	16.35	15.70	14.87	651-3118135	-	651-1205053	651-0800886	NS 35
651-3004142	3004142	B	UK 5 HESILA 250	Fuse Block with LED, 110-250V	16.35	15.70	14.87	651-3118135	-	651-1205053	651-0800886	NS 35
651-3004171	3004171	C	UK 6.3 HESI	Fuse Block	13.17	12.65	11.99	651-0203137	-	651-1205066	651-0800886	NS 35
651-3004265	3004265	C	UK 6.3 HESI/LED 24	Fuse Block with LED, 15-30V	17.73	16.18	15.24	651-0203137	-	651-1205066	651-0800886	NS 35
651-3004249	3004249	C	UK HESILA 250	Fuse Block with LED, 110-250V	17.73	16.18	15.24	651-0203137	-	651-1205066	651-0800886	NS 35
651-3048386	3048386	D	UK 10.3 HESI N	Fuse Block	14.75	13.60	12.80	651-3009299	-	651-1205066	651-0800886	NS 35
651-3048399	3048399	D	UK 10.3 HESI/LED N 690	Fuse Block with LED, 220-690V	24.40	22.49	21.18	651-3009367	-	-	-	-
651-3007204	3007204	E	UKK 5 HESI (5x20)	Fuse Block	19.53	17.82	16.78	-	651-2772080	651-1205053	651-0800886	NS 35
651-0711629	0711629	E	UKK 5 HESILA 250 (5x20)	Fuse Block with LED, 110-250V	31.85	29.34	26.82	-	651-2772080	651-1205053	651-0800886	NS 35
651-3007217	3007217	F	UKK 5 HESI (6.3x32)	Fuse Block	20.45	18.66	17.57	-	651-2772080	651-1205053	651-0800886	NS 35
651-0711632	0711632	F	UKK 5 HESI/LED 24 (6.3x32)	Fuse Block with LED for 15-30V	31.90	29.39	26.87	-	651-2772080	651-1205053	651-0800886	NS 35
651-0711616	0711616	F	UKK5 HESILA 250 (6.3x32)	Fuse Block with LED, 110-250V	25.45	25.45	25.45	-	651-2772080	651-1205053	651-0800886	NS 35

Terminal Blocks

DIMENSIONS: mm

A		B	
DIKD 1.5TG <ul style="list-style-type: none"> Width: 6.2mm 30-14AWG (UL) 15A (UL) 3 Levels 		DIK 1.5 <ul style="list-style-type: none"> Width: 6.2mm 30-14AWG (UL) 15A (UL) 3 Levels 	
C		D	
DIKD 1.5 <ul style="list-style-type: none"> Requires fuse Plug Width: 6.2mm 28-12AWG (UL) 6.3A (UL) 		UDK 4-TG <ul style="list-style-type: none"> Requires fuse Plug Width: 6.2mm 26-12AWG (UL) 15A (UL) 15A upper/ 25A lower (UL) 	
		E	
		UKKS-TG <ul style="list-style-type: none"> Requires fuse Plug Width: 6.2mm 30-14AWG (UL) 15A (UL) 3 Levels 	

THREE LEVEL SENSOR TERMINAL BLOCKS

Color: Gray • 300V (UL)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Phoenix Part No.	Fig.	Phoenix Type	Price Each			Accessories (See Accessories page for pricing and descriptions)								
				1	10	50	Partition Plate	Fixed Bridge	Insertion Bridge	Fuse			Screwdriver	End Bracket	Din Rail Type
								Plug	30V Light	250V Light					
651-2774237	2777014	A	DIKD 1.5 TG	11.33	10.89	10.04	651-1413285	651-2715953	651-2715940	651-0921011	651-0921037	651-0921053	651-1205053	651-0800886	NS 35
651-2715966	3007042	B	DIK 1.5	6.15	5.91	5.44	651-1413272	651-0203250, 651-2715953	651-2715940	-	-	-	651-1205053	651-0800886	NS 35
651-2715979	3007042	C	DIKD 1.5	10.73	10.31	9.50	651-1413285	651-0203250, 651-2715953	651-2715940	-	-	-	651-1205053	651-0800886	NS 35

BASE TERMINAL BLOCKS FOR CARTRIDGE FUSE

Color: Gray • 300V (UL)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Phoenix Part No.	Fig.	Phoenix Type	Price Each			Accessories (See Accessories page for pricing and descriptions)								
				1	10	50	End Cover	Partition Plate	Bridge		Fuse		Screwdriver	End Bracket	Din Rail Type
								Fixed	Insertion	Plug	30V Light				
651-2777014	2777014	D	UDK 4-TG	6.29	6.13	5.73	651-2777027	-	651-0203250	651-0201139	651-0921011	651-0921037	651-0921053	651-0800886	NS 35
651-3007042	3007042	E	UKK 5-TG	16.48	15.83	14.59	-	-	651-0203250	651-0201139	651-0921011	651-0921037	651-0921053	651-0800886	NS 35