

PRODUCT SHEET

Steel City® double snap-in connectors

Speed. Strength. Simplicity.

Steel City®



Steel City double snap-in connectors deliver fast, code-compliant terminations for residential, commercial, retrofit and industrial applications. Designed for quick, tool-free installation, they ensure a secure, durable connection between your electrical box and cable — ideal for use with aluminum or steel armored cable, metal-clad cable, flexible metal conduit or reduced wall flexible metal conduit.



Tool-free, snap-in design installs quickly



90° versions are ideal for tight bends



Reusable and repositionable



Designed for fast, code-compliant cable terminations

Key features

- 1 Cut-in and 90° options** — For directional flexibility and retrofit installs
- 2 Install easily with spring tabs in ½" knockouts** — No tools or locknuts required
- 3 Reuse or reposition** — Easily removed from knockouts
- 4 Pre-installed insulators** — Durable plastic inserts protect conductors and won't fall out
- 5 Concrete-tight** — Secure when taped, meeting jobsite and code requirements
- 6 Multiple cable support** — Support one or two runs depending on model

**ENGINEERED
TO OUTRUN**




Catalog no.	XC-140	XC-150	XC-160	XC-170	XC-180
Description	3⁄8" double snap-in single cable connector	3⁄8" double snap-in squeeze lock connector	3⁄8" cut-in double snap-in connector	3⁄8" 90° double snap-in squeeze lock connector	1⁄2" 90° double snap-in squeeze lock connector
Use case	Standard cable runs	Dual cable terminations in a single knockout	Retrofit/old work installs	Tight bends and directional runs	Tight bends and directional runs
Terminates (aluminum or steel)	AC 14-2 to 10-2; MC/MCI-A/HCF 14-2 to 10-3; 3⁄8" FMC and RWFMC	AC 14-2 to 10-3; MC/MCI-A/HCF 14-2 to 10-3; 3⁄8" RWFMC	AC 14-2 to 10-3; MC/MCI/HCF 14-2 to 10-3	AC 14-2 to 10-3; MC/MCI-A/HCF 14-2 to 10-4; 3⁄8" RWFMC	AC 8-2 to 8-3; MC/MCI-A/HCF 8-2 to 8-3; 1⁄2" RWFMC
Std. ctn. qty.	50	50	50	25	25
UPC no.	708917419372	708917419389	708917419396	708917419402	708917419419


Install AC or MC cable in tight spots easily with a 90° double snap-in squeeze lock connector



Connector with latch closed



Connector with latch open



Connector with latch open and AC or MC cable inserted



Connector with latch closed and AC or MC cable installed

Steel City®▶ products with
THE METAL
for the job

ABB Installation Products Inc.
Electrification Business
860 Ridge Lake Blvd.
Memphis, TN 38120

electrification.us.abb.com

ABB has made every attempt to ensure the accuracy and reliability of the contents of this document. However, all content is provided for general informational purposes only, and ABB makes no guaranty or warranty, express or implied, as to the accuracy of any technical content, or that the information contained in this publication will be error free and all such guarantees or warranties are expressly

disclaimed. ABB may change or modify the contents at any time, without prior notice. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents — in whole or in parts — is forbidden without prior written consent of ABB.
© 2025 ABB Installation Products Inc. and/or its related companies All rights reserved