

TMP-B SXX12-XXXXPCXXX

KEYING OPTIONS	
A	LIGHT BROWN
B	RED
C	BLUE
D	GREEN


CONTACT FINISH	
0	GOLD

TERMINATION SIZE	
0	STANDARD



INSERT CODE	
005A	5 POSITION, STD
018A	18 POSITION, STD

HOUSING FINISH	
N	TIN NICKEL


HOUSING MATERIAL	
A	ALUMINUM



ISOMETRIC VIEW
FOR REFERENCE ONLY
TMP-B SAN12-018APC00A SHOWN





KEYING OPTIONS (VIEW LOOKING AT PLUG FACE)




- NOTES:
- 1. SEE ESG6092 FOR MATERIAL AND PERFORMANCE SPECIFICATIONS
 - 2. SEE ESG6093 FOR ASSEMBLY INSTRUCTIONS
 - 3. SIZE 16 PIN CONTACTS PER M39029/58-364
 - 4. SIZE 22D PIN CONTACTS PER M39029/58-360
 - 5. SIZE 20MD PIN CONTACTS PER AIRBORN TMC-P20MD



MATERIAL: SEE NOTES Temper: Per Spec.: R/M P/N ref: N/A Certification required: NO		UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE: Decimals: .XX ± 0.01 Concentricity: Decimals: .XXX ± 0.008 Angles: ± 1° Decimals: .XXXX ± 0.0040 Radius: ± Parts are to be symmetrical about centerline within ± .005 Surfaces to be flat, perpendicular parallel within .004 T.I.R. Dimensions are in inches/DO NOT SCALE PRINT Surface finish to be  or better				AirBorn Georgetown, Texas 78626		Cage Code 10400			
HEAT TREAT: SEE NOTES Per Spec.: Certification required: NO		APPLICATION: TRIMATE SERIES				DRAWING STATE: Released This drawing is not authorized for production unless it is released		<input checked="" type="checkbox"/> RELEASED			
FINISH: SEE NOTES Per Spec.: Certification required: NO		- INITIAL RELEASE		CC 060923	CC 060923	DR. CC 060923	T I T L E	PLUG, SIZE 12 BREAK AWAY, 1ST PINS, CRIMP		SIZE C	
		REV DESCRIPTION		DR. BY DATE	ECO NO. APPD. BY	CK. RCS 060923					
MAKE FROM: N/A NEXT ASSY: N/A		▶ - CRITICAL CHARACTERISTIC ● - MAJOR CHARACTERISTIC		THIRD ANGLE PROJECTION		REL. CC 060923	APPD. RCS 060923	DWG# TMP-BSXX12-XXXXPCXXX		REV. -	SHEET 1/3

TMP-B SXX12-XXXXPCXXX


INSERT CODE	
005A	5 POSITION, STD



INSERT ARRANGEMENT 005A
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A

TMP-B SXX12-XXXXPCXXX

INSERT CODE	
018A	18 POSITION, STD



INSERT ARRANGEMENT 018A
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A