

'D' Series Hoods

LT & LTM TYPE HOODS

A screw together two piece hood, moulded in flame retardent UL94V material available in various colour options or metalised version. The hood is supplied complete with jack screws and internal cable clamp.

SHELL	SIZE	PART NUMBER	OUTLINE DIMENSIONS			
			A	B	C	D
9	23	LT09*	17	17	95.0	
15	33	LT15*	17	33.3	47.0	
25	37	LT25*	17	47.0	63.5	
37	39	LT37*	17	63.5	61.1	
50	39	LT50*	19	68	61.1	

*For colour options add the following suffix to part number Y for Yellow, R for Red, BL for Blue, GR for Grey.

C TYPE HOODS

A screw together two piece hood, moulded in flame retardent UL94V material available in black finish only. The hood features top or side cable entry options with external cable clamping. For suitable side locks see 'E' type opposite.

SHELL	SIZE	PART NUMBER	OUTLINE DIMENSIONS			
			A	B	C	D
9	29	C09	15	25.0		
15	35	C15	15	33.3		
25	39	C25	15	47.0		
37	46	C37	15	63.5		
50	46	C50	18	61.1		

ET TYPE HOODS



A screw together two piece hood, moulded in flame retardent UL94V material available in black finish only. The hood is supplied complete with jack screws and external cable clamps.

SHELL	SIZE	PART NUMBER	OUTLINE DIMENSIONS			
			A	B	C	D
9	31	ET09	19	25.0		
15	38	ET15	19	33.3		
25	44	ET25	19	47.0		



SF TYPE HOODS

A snap together two piece hood, moulded in flame retardent UL94V material available in black finish only. The hood features triple cable entry option and is supplied with a screw together cable clamp, two cable entry blanking plates and two cable ties.



SHELL	SIZE	PART NUMBER	OUTLINE DIMENSIONS			
			A	B	C	D
9	53	SF09	17	13		
15	53	SF15	17	19		
25	53	SF25	17	30		





LT & LTM TYPE



C TYPE



ET TYPE



SF TYPE

E TYPE SLIDELOCKS & FB LATCHES

The 'E' type slidelocks provide an effective fast operating latch mechanism for 'C' type hoods when used in conjunction with the 'FB' latches. Slide locks are supplied with spring return mechanism, latches are supplied in pairs.

SLIDELOCKS				LATCHES			
Part No.	E09	E15	E25	Part No.	FB9-37	FB50	
Shell Size	9	15	25	Shell Size	9-37	50	

Hardware & Mounting Accessories

