

MagicTip Safety Ring Pliers-External



SHOP

346 MagicTip Straight External Safety Ring Pliers DIN ISO 5254

Shape A, straight tips. Precision machined tips of Chrome-vanadium special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item No.	mm	Inch	Inch	mm	Tip Inch/mm	Pkg.	lbs.
34620	185	7.3	3/4-2 3/8	19-60	.070/1.5	1	.34
34621	240	9.5	1 1/2-4	40-100	.090/2.3	1	.57
34622	300	11.8	3.5-5.5	85-140	.126/3.2	1	1.04

MagicTip 90° Angle Safety Ring Pliers - External




SHOP

346 MagicTip 90° Angled External Safety Ring Pliers DIN ISO 5254

Shape B, 90° angled tips. Precision machined tips of Chrome-vanadium special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item No.	mm	Inch	Inch	mm	Tip Inch/mm	Pkg.	lbs.
34625	185	7.3	3/4-2 3/8	19-60	.070/1.5	1	.36
34626	240	9.5	1 1/2-4	40-100	.090/2.3	1	.57
34627	300	11.8	3.5-5.5	85-140	.126/3.2	1	1.06



In Canvas
Roll-Up
Pouch

SHOP

34697 6 Pc. Straight Internal & External Ring Pliers Set

Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing retaining rings. Soft vinyl grips

Item#	34697	Set Includes:	lbs. 4.04
34610	3/4-2-3/8" / 19-60mm / tip .070	34620 3/4-2-3/8" / 19-60mm / tip .070	
34611	1-1/2-4" / 40-100mm / tip .090	34621 1-1/2-4" / 40-100mm / tip .090	
34612	3.5-5.5" / 85-140mm / tip .126	34622 3.5-5.5" / 85-140mm / tip .126	




In Canvas Roll-Up Pouch

SHOP

34699 12 Pc. Straight And 90° Internal & External Ring Pliers Set

Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing retaining rings. Soft vinyl grips

Item#	34699	Set Includes:	lbs. 8.52
34610	3/4-2-3/8" / 19-60mm / tip .070	34620 3/4-2-3/8" / 19-60mm / tip .070	
34611	1-1/2-4" / 40-100mm / tip .090	34621 1-1/2-4" / 40-100mm / tip .090	
34612	3.5-5.5" / 85-140mm / tip .126	34622 3.5-5.5" / 85-140mm / tip .126	
34615	3/4-2-3/8" / 19-60mm / tip .070	34625 3/4-2-3/8" / 19-60mm / tip .070	
34616	1-1/2-4" / 40-100mm / tip .090	34626 1-1/2-4" / 40-100mm / tip .090	
34617	3.5-5.5" / 85-140mm / tip .126	34627 3.5-5.5" / 85-140mm / tip .126	



In Canvas
Roll-Up
Pouch

SHOP

34698 6 Pc. 90° Angle Internal & External Ring Pliers Set

Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing retaining rings. Soft vinyl grips

Item#	34698	Set Includes:	lbs. 4.06
34615	3/4-2-3/8" / 19-60mm / tip .070	34625 3/4-2-3/8" / 19-60mm / tip .070	
34616	1-1/2-4" / 40-100mm / tip .090	34626 1-1/2-4" / 40-100mm / tip .090	
34617	3.5-5.5" / 85-140mm / tip .126	34627 3.5-5.5" / 85-140mm / tip .126	