






1	2	3	4	5				
	SUB ASSEMBLY PART NO.	NO.	PART NO.	PART NAME	MATERIAL	COLOR	QTY.	YAZAKI MATING PART NO.
	7282-6454-40	①	7182-6454-40	1.5 SYSTEM CONNECTOR 6P (M) HOUSING	PBT-GF15	LIGHT GREY	1	7283-6454-40
		②	7158-5982	1.5 SYSTEM CONNECTOR 6P (M) FRONT HOLDER	PBT	NATURAL	1	
	7282-6454-50	①	7182-6454-50	1.5 SYSTEM CONNECTOR 6P (M) HOUSING	PBT-GF15	ORANGE	1	7283-6454-50
		②	7158-5982	1.5 SYSTEM CONNECTOR 6P (M) FRONT HOLDER	PBT	NATURAL	1	
	7282-6454-70	①	7182-6454-70	1.5 SYSTEM CONNECTOR 6P (M) HOUSING	PBT-GF15	YELLOW	1	7283-6454-70
		②	7158-5982	1.5 SYSTEM CONNECTOR 6P (M) FRONT HOLDER	PBT	NATURAL	1	



NOTES:
1. APPLICABLE TERMINAL PART NO.: 7114-4100-02 ETC.
2. MATING PART NO.: SEE TABLE.
3. THE MATERIALS USED IN THIS PRODUCT ARE IN CONFORMITY WITH REQUIREMENTS OF EU ELV 2000/53/EC DIRECTIVE AND ASSOCIATED DOCUMENTS.



SECTION A-A



ISOMETRIC VIEW

(SCALE 1:1)

ISSUE MARK

LET	DATE	REVISION RECORD	NO.	CHKD
△	13.05.2013.	ADDED 7282-6454-50 & -70	Y13-0272	G.G.
△	09.09.2002.	NEW	C02-E301	M.K.

GENERAL TOLERANCE									
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1	R	NEW
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1	APPROVED	CHECKED
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15	T.SCHALLER	G.GREGURIC
SPECIFIED							MASS	8.2 g	114.05.2013

CUSTOMER							MATERIAL SPEC. SEE TABLE			TREAT. & FIN.	
CUSTOMER PART NO.				CUSTOMER DWG NO.			NAME 1.5 SYSTEM CONNECTOR				
OFFICE				TRIAL PART NO.			6P (M) SUB ASSEMBLY				
VENDOR											
VENDOR NO.											
DWG TYPE		DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE	PART NO. CH. CODE 7282-6454-40, ETC.		
R		NEW		21.01.2003		mm	2/1	3	DWG NO. 7282-6454-40:R SET DWG NO.		
APPROVED		CHECKED		DESIGN		DRAWN					
T. SCHALLER		G. GREGORIC		M. KASHIYAMA		G. GREGORIC					
22.05.2015		14.05.2013		21.01.2003		13.05.2013					