

## ComfortGrip Slide Lock Adjustable Pliers

With box joint



Rapid adjust

- Close to lock
- Open and slide to adjust opening size
- Audible click at each locking position



### 32969 Slide Lock Adjustable Pliers - Wiha QuickFix - Box Joint

**DIN ISO 8976** Super fast and easily adjusted pliers. Long durability achieved through additional induction hardening of jaws to approx. 56 HRC. Finger jam protection for safe operation at all settings. Chrome-vanadium tool steel forgings, hardened and tempered. Chrome finish with ergonomic ComfortGrip handles.

Item	↔	↔	Capacities		↔	↔
No.	mm	Inch	Round	Hex	Pkg.	lbs.
32969	250	10.0	1 1/4"	1 1/2"	1	.80

## Industrial SoftGrip Pliers & Cutters Sets



### 30993 3 Piece Industrial SoftGrip Pliers & Cutters Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30993 Set Includes:	↔
30905 Combination Pliers - 8.0"	lbs.
30925 Diagonal Cutters - 6.3"	1.76
30911 Long Nose Pliers - 6.3"	



### 30990 4 Piece Industrial SoftGrip Pliers & Cutters Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30990 Set Includes:	↔
9.0" - Heavy Duty Combination Pliers	lbs.
8.0" - Long Nose Pliers	2.81
8.0" - High Leverage Diagonal Cutters	
7.0" - ComfortGrip Stripping Pliers	

## Industrial SoftGrip Pliers & Cutters Sets



### 30998 8 Piece Industrial SoftGrip Pliers & Cutters Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30998 Set Includes:	↔
6.3" - Combination Pliers	lbs.
9.0" - Heavy Duty Combination Pliers	4.91
6.3" - Long Nose Pliers	
8.0" - Long Nose Pliers	
5.5" - Diagonal Cutters	
8.0" - High Leverage Diagonal Cutters	
10.0" - Adjustable Pliers	
7.0" - ComfortGrip Stripping Pliers	



### 30991 18 Piece Industrial SoftGrip Pliers/Cutters, Screwdrivers & Wrenches Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30991 Set Includes:	↔
8.0" - Combination Pliers	lbs.
6.3" - Long Nose Pliers	6.76
6.3" - Diagonal Cutters	
10.0" - Adjustable Pliers	
Slotted: 5/32, 1/4" Phillips: 1, 2	
Torx: T15, T20, T25 Square: 1, 2	
Wrenches: 1/4"x5/16", 3/8x7/16", 1/2x9/16", 3/4x7/8"	