





004 & 113 SERIES FOR 15/32" MOUNTING HOLE • LIGHT SHIELD

BASE PART NO.	VOLTAGE	FIG
004-1830-29-203	1.35-28	1
004-1930-29-203	1.35-28	2



Uses:
T-1 3/4 MIDGET
FLANGE BASE
INCANDESCENT
LAMP



CAP PART NO.	COLOR	FIG	CAP PART NO.	COLOR	FIG
004-2900-200	NO LENS	3	113-2931-203	RED	4
			113-2937-203	CLEAR	4



Material & Finish: Base - Black Nickel Plated Brass,
Cap - Black Nickel Plated Brass with High Impact Plastic Lens




101, 111, 140 SERIES FOR 15/32" MOUNTING HOLE • WATERTIGHT

BASE PART NO.	VOLTAGE	FIG
101-3830-09-203	1.35-28	5
101-8430-09-203	1.35-28	6



Uses:
T-1 3/4 MIDGET
FLANGE BASE
INCANDESCENT
LAMP OR BASED
LED LAMP**

CAP PART NO. *	COLOR	FIG	CAP PART NO. *	COLOR	FIG
101-0937-003	CLEAR	7	111-0113-203	AMBER	8
101-0971-003	RED	7	111-0135-203	WHITE	8
101-0972-003	GREEN	7	111-0137-203	CLEAR	8
101-0973-003	AMBER	7	140-1437-003	CLEAR	9
101-0975-003	WHITE	7	140-1471-003	RED	9
111-0111-203	RED	8	140-1472-003	GREEN	9
111-0112-203	GREEN	8	140-1473-003	AMBER	9
			140-1475-003	WHITE	9



Material & Finish: Base - Black Nickel Plated Brass, Cap - High Impact Plastic;
Polycarbonate with Black Nickel Bezel (Fig. 8)

**** Dialight recommends: Transparent lens caps for Based LEDs; Clear lens caps for Green Based LEDs**


*PART NUMBER ORDERING CODE	
101 - 09xx - 003	
140 - 14xx - 003	
Series	Lens Finish:
	3 = Transparent**
	7 = Translucent
	(Not available in clear)

*PART NUMBER ORDERING CODE	
111 - 01xx - 203	
Series	Lens Finish:
	1 = Back Frosted
	(Not available in white)
	3 = Transparent**

812 SERIES FOR 15/32" MOUNTING HOLE • PRESS-TO-TEST

BASE PART NO.	VOLTAGE	FIG
812-1030-09-506	1.35-28	10

CAP PART NO. *	COLOR	FIG
812-0937	CLEAR	11
812-0971	RED	11
812-0972	GREEN	11
812-0973	AMBER	11
812-0975	WHITE	11



Uses:
T-1 3/4 MIDGET FLANGE BASE
INCANDESCENT LAMP OR BASED
LED LAMP**

Material & Finish: Base - Black Anodized
Aluminum, Cap - High Impact Plastic

**** Dialight recommends: Transparent lens caps for
Based LEDs; Clear lens caps for Green Based LEDs**

*PART NUMBER ORDERING CODE	
812 - 09xx	
Series	Lens Finish:
	3 = Transparent**
	7 = Translucent
	(Not available in clear)

Neon and incandescent lamp information on Pages 35 and 36.
Based LED lamp information on Pages on 37 through 40.

Dimensions in mm [inches]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

101-0971-003