




■Single Row Straight Pin Header (SMT) (Three-Wall/Correspond to Vacuum Absorption)



Note:"No guide post" indicates the style with no boss.

◆PCB mounting pattern



Note 1.This hole isn't needed for "No guide post".
Note 2.If the pattern exists in the shaded area, and isn't treated with resist, it could touch the connector contact.

[Specific No.] – **, (**)
(20): Tin plated tube packaging
(21): Tin plated embossed tape packaging
(50): Gold plated tube packaging
(51): Gold plated embossed tape packaging

Unit: mm

Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	Tube Packaging Quantity	Emboss Width	Remarks
DF13B- 2P-1.25V(**)	536-0051-2**	2	1.25	4.15	7.15	3.35	5.65	1.95	2.20	67pcs	16	With boss
DF13B- 3P-1.25V(**)	536-0052-5**	3	2.50	5.40	8.40	4.60	6.90	3.20	3.45	57	16	
DF13B- 4P-1.25V(**)	536-0053-8**	4	3.75	6.65	9.65	5.85	8.15	4.45	3.10	49	24	
DF13B- 5P-1.25V(**)	536-0054-0**	5	5.00	7.90	10.90	7.10	9.40	5.70	4.35	44	24	
DF13B- 6P-1.25V(**)	536-0055-3**	6	6.25	9.15	12.15	8.35	10.65	6.95	5.60	39	24	
DF13B- 7P-1.25V(**)	536-0056-6**	7	7.50	10.40	13.40	9.60	11.90	8.20	6.85	36	24	
DF13B- 8P-1.25V(**)	536-0057-9**	8	8.75	11.65	14.65	10.85	13.15	9.45	8.10	33	24	
DF13B- 9P-1.25V(**)	536-0058-1**	9	10.00	12.90	15.90	12.10	14.40	10.70	9.35	30	24	
DF13B-10P-1.25V(**)	536-0059-4**	10	11.25	14.15	17.15	13.35	15.65	11.95	10.60	28	24	
DF13B-11P-1.25V(**)	536-0060-3**	11	12.50	15.40	18.40	14.60	16.90	13.20	11.85	26	32	
DF13B-12P-1.25V(**)	536-0061-6**	12	13.75	16.65	19.65	15.85	18.15	14.45	13.10	24	32	
DF13B-14P-1.25V(**)	536-0063-1**	14	16.25	19.15	22.15	18.35	20.65	16.95	15.60	21	32	
DF13B-15P-1.25V(**)	536-0064-4**	15	17.50	20.40	23.40	19.60	21.90	18.20	16.85	20	44	
DF13C- 2P-1.25V(**)	536-0401-2**	2	1.25	4.15	7.15	—	5.65	1.95	2.20	67pcs	16	Without boss
DF13C- 3P-1.25V(**)	536-0402-5**	3	2.50	5.40	8.40	—	6.90	3.20	3.45	57	16	
DF13C- 4P-1.25V(**)	536-0403-8**	4	3.75	6.65	9.65	—	8.15	4.45	3.10	49	24	
DF13C- 5P-1.25V(**)	536-0404-0**	5	5.00	7.90	10.90	—	9.40	5.70	4.35	44	24	
DF13C- 6P-1.25V(**)	536-0405-3**	6	6.25	9.15	12.15	—	10.65	6.95	5.60	39	24	
DF13C- 7P-1.25V(**)	536-0406-6**	7	7.50	10.40	13.40	—	11.90	8.20	6.85	36	24	
DF13C- 8P-1.25V(**)	536-0407-9**	8	8.75	11.65	14.65	—	13.15	9.45	8.10	33	24	
DF13C- 9P-1.25V(**)	536-0408-1**	9	10.00	12.90	15.90	—	14.40	10.70	9.35	30	24	
DF13C-10P-1.25V(**)	536-0409-4**	10	11.25	14.15	17.15	—	15.65	11.95	10.60	28	24	
DF13C-11P-1.25V(**)	536-0410-3**	11	12.50	15.40	18.40	—	16.90	13.20	11.85	26	32	
DF13C-12P-1.25V(**)	536-0411-6**	12	13.75	16.65	19.65	—	18.15	14.45	13.10	24	32	
DF13C-14P-1.25V(**)	536-0413-1**	14	16.25	19.15	22.15	—	20.65	16.95	15.60	21	32	
DF13C-15P-1.25V(**)	536-0414-4**	15	17.50	20.40	23.40	—	21.90	18.20	16.85	20	44	

Note 1.Please order the tube packaging product, multiplying the tube packaging quantity.

Note 2.Please order the embossed tape packaging product according to reel number. (1000 pcs. per reel)