


930 - 004 F 10

Product Series _____

Basic Number _____

Dash Number (Table I) _____

Material Symbol (Table II) _____

**NOTES:**

1. Identified by bag and tag in suitable quantities.
2. Metric dimensions (mm) are indicated in parentheses.

930-004
Gasket for MIL-DTL-5015 and MIL-C-22992
Class C - J and R Receptacle Connectors



Miscellaneous
Accessories

TABLE I: DASH NUMBER

MIL-C-22992												
Dash		Class C	A		B Dia		C		D Dia		F Rad	
No.	MIL-DTL-5015	J & R	±.010	(0.3)	+0.016 -.0	(+0.4 -.0)	+0.016 -.0	(+0.4 -.0)	±.010	(0.1)	±.010	(0.3)
1	8S	-	.594	(15.1)	.500	(12.7)	.875	(22.2)	.172	(4.4)	.141	(3.6)
2	10S & 10SL	-	.719	(18.3)	.625	(15.9)	1.000	(24.4)	.172	(4.4)	.141	(3.6)
3	12 & 12S	-	.812	(20.6)	.750	(19.1)	1.094	(27.8)	.172	(4.4)	.141	(3.6)
4	14 & 14S	12	.906	(23.0)	.875	(22.2)	1.188	(30.2)	.172	(4.4)	.141	(3.6)
5	16 & 16S	14	.969	(24.6)	1.000	(25.4)	1.281	(32.5)	.172	(4.4)	.156	(4.0)
6	18	16	1.062	(27.0)	1.125	(28.6)	1.375	(34.9)	.203	(5.2)	.156	(4.0)
7	20	18	1.156	(29.4)	1.250	(31.8)	1.500	(38.1)	.203	(5.2)	.172	(4.4)
8	22	20	1.250	(31.8)	1.375	(34.9)	1.625	(41.3)	.203	(5.2)	.188	(4.8)
9	24	22	1.375	(34.9)	1.500	(38.1)	1.750	(44.5)	.203	(5.2)	.188	(4.8)
10	28	24	1.562	(39.7)	1.750	(44.5)	2.000	(50.8)	.203	(5.2)	.219	(5.6)
11	28	-	2.188	(55.6)	1.750	(44.5)	2.688	(68.3)	.203	(5.2)	.250	(6.4)
12	32	28	1.750	(44.5)	2.000	(50.8)	2.250	(57.6)	.219	(5.6)	.250	(6.4)
13	36	32	1.938	(49.2)	2.188	(55.6)	2.500	(63.5)	.219	(5.6)	.281	(7.1)
14	40	36	1.188	(30.2)	2.438	(61.9)	2.750	(69.9)	.219	(5.6)	.281	(7.1)
15	18*	-	1.062	(27.0)	1.220	(31.0)	1.375	(34.9)	.203	(5.2)	.156	(4.0)

*Fits Amphenol GT Series

TABLE II: MATERIAL

Symbol	Material Description
C	Conductive — Metex
F	Fluorosilicone
M	Conductive — Con-Sil II
N	Neoprene
S	Silicone

Metric Dimensions (mm) are indicated in parenthesis.