








Printed board layout
component side



A

09 66 211 6501	M3	2					Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-sub, 15 poles, female, straight, with solder pins 2.9, and nuts.	Maßstab/ Scale 1,5:1
09 66 211 7501	M3	3					Detail.	05/03/02	CV		
09 66 211 5501	M3	0,76 µm Au					Insp.				
09 66 211 6502	4-40 UNC	2					Stand.				
09 66 211 7502	4-40 UNC	3								TB 09 66 211 x50x	Blatt/ Page 2
09 66 211 5502	4-40 UNC	0,76 µm Au	29723	05/03/02	CV						
Part number	Nut thread	Performance level	Mod.	Dat.	Name						

HARTING EURL
F-95972 Paris



Sub.

09 66 211 6501
D-Sub - S PCB connector

Other applications

gender	female connector, straight
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Board fixing	without grounding board locks
flange	M 3
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 211 5502
D-Sub - S PCB connector

Other applications

gender	female connector, straight
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Board fixing	without grounding board locks
flange	UNC4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 211 5501
D-Sub - S PCB connector

Other applications

gender	female connector, straight
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Board fixing	without grounding board locks
flange	M 3
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



Data sheets are available in following formats
2D files

Typenblatt

Typenblatt

09 66 211 6502
D-Sub - S PCB connector

Other applications

gender	female connector, straight
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Board fixing	without grounding board locks
flange	UNC4-40
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 211 7501
D-Sub - S PCB connector

Other applications

gender	female connector, straight
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Board fixing	without grounding board locks
flange	M 3
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 211 7502
D-Sub - S PCB connector

Other applications

gender	female connector, straight
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Board fixing	without grounding board locks
flange	UNC4-40
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF