



IPA-Based Presaturated Wipes IsoClean™



- Cleans water-based, rosin, and no-clean fluxes
- 99.8% pure IPA saturated lint-free wipes
- Ultra-pure, no residues
- Medium drying for maximum cleaning time
- Plastic-safe

Product Information

The IPA-Based Presat Wipes - *IsoClean* are a plastic-safe, non-corrosive, ESD-safe circuit cleaner that quickly and easily removes fluxes, pastes, light oils and grease, as well as organic residues. It is effectively used as a circuit cleaner and stencil cleaner.

MicroCare IPA-Based Presat Wipes - *IsoClean* are the strongest IPA-based cleaner on the market. While most IPA-based cleaners contain up to 30% water, this cleaner contains virtually no water and is undiluted by airborne humidity. 100% volatile, it evaporates cleanly with no rinsing required.

It is safe on all materials including components, connectors, cables and elastomers.

AVAILABILITY: Stocked by MicroCare distributors world-wide. Contact MicroCare for a distributor near you. For more information contact MicroCare directly or visit www.MicroCare.com.

Discover Perfectly Clean www.MicroCare.com

MicroCare Corporation

595 John Downey Drive
New Britain, CT 06051 USA
CAGE: OATV9
Tel: +1 860 827 0626
Toll Free: 1 800 638 0125
Email: TechSupport@MicroCare.com

MicroCare Europe BVBA

Vekestraat 29 B11
Industriezone 't Sas
1910 Kampenhout, Belgium
Tel: +32 2 251 95 05
Email: EuroSales@MicroCare.com

MicroCare U.K. Ltd

Seven Hills Business Park,
Morley,
Leeds, West Yorkshire, UK
LS27 8AT
Tel: +44 (0) 113 3501008
Email: mcceurope@microcare.com

MicroCare Asia Pte Ltd

102E Pasir Panjang Road
#03-01 Citilink Warehouse Complex
Singapore 118529
Tel: +65 6271 0182
Email: TechSupport@MicroCare.sg

Technical Details and Cleaning Data	
Boiling Point	83 °C / 174 °F
Chemical Family	Alcohol
Cleaning Strength (KB value)	20
Evaporation Rate	Medium
Odor	Slight, Alcohol
Percent Volatile	100%
Specific Gravity	0.79
Health, Safety and Environmental Data	
Flammable	Yes
Flashpoint	12 °C / 53 °F
NFPA	Health: 1 Fire: 3 Instability: 1
RoHS and WEEE Compliant	Yes
REACH	Yes*
US EPA SNAP-Approved	Yes
GHS / HCS Pictogram	 
Packaging	
Aerosol ¹ - 12 oz / 340 g	MCC-BAC
Minicube ² - 6 lb / 2.72 kg	MCC-BACG
Gallon Jug ³ - 6 lb / 2.72 kg	MCC-BACJG
Cube ² - 32 lb / 14.5 kg	MCC-BACP
Drum ¹ - 355 lb / 161 kg	MCC-BACD
Presaturated Wipes ³ 443 mls. fluid content	100 - 5" x 8" Wipes MCC-BACW
Presaturated Wipe Refills 443 mls. fluid content	100 - 5" x 8" Wipes MCC-BACWR
Shelf Life	Unlimited
Recycle	  

*Contact MicroCare for specific details

Money-saving refills reduce costs and help protect the environment by reducing waste and encouraging the re-use of packaging.

