



General Purpose Dust Remover

- Cleans dust & grit from keyboards, optics, machinery & circuitry
- Nonflammable
- High-pressure
- High-purity, leaves no residue
- Multiple package sizes available
- Highly economical



Product Information

General Purpose Dust Remover is a high purity electronics-grade cleaner that delivers a dry blast of inert gas to hard to reach surfaces. Use to remove dust, particles, and moisture from any surface.

Clean hard-to-reach areas like keyboards or pin connectors. Use to quickly pre-clean surfaces by removing layers of loose grime and dust before using a solvent cleaner. Also, use to remove slow-drying solvents from under surface mount components or on circuit boards, connectors or optics. There are literally hundreds of uses.

Available in a variety of sizes and spray velocities to fit any cleaning need. The trigger spray allows easy single-handed operation. Plastic-safe, nonflammable and leaves no residue.

Packaging

Product	Contents	Ultra-Low GWP	High-Pressure	360 Invertible	StatZap™ Compatible
MCC-DST*	10oz / 280g		X		
MCC-DSTZ	10oz / 280g				X
MCC-DST08A	8oz / 227g			X	
MCC-DST087	8oz / 237g	X		X	
MCC-DSTZ14	14oz / 392g				X
MCC-DST14A	14oz / 392g		X		
MCC-DST107	10oz / 280g	X			

* MCC-DST = NSN 6850-01-483-4104

Discover Perfectly Clean www.MicroCare.com

MicroCare Corporation

595 John Downey Drive
New Britain, CT 06051 USA
CAGE: OATV9
Tel: +1 860 827 0626
Toll Free: 1 800 638 0125
Email: TechSupport@MicroCare.com

MicroCare Europe BVBA

Vekestraat 29 B11
Industriezone 't Sas
1910 Kampenhout, Belgium
Tel: +32 2 251 95 05
Email: EuroSales@MicroCare.com

MicroCare U.K. Ltd

Seven Hills Business Park,
Morley,
Leeds, West Yorkshire, UK
LS27 8AT
Tel: +44 (0) 113 3501008
Email: mcceurope@microcare.com

MicroCare Asia Pte Ltd

102E Pasir Panjang Road
#03-01 Citilink Warehouse Complex
Singapore 118529
Tel: +65 6271 0182
Email: TechSupport@MicroCare.sg

Technical Details and Cleaning Data	
Chemical Family	HFO or HFC
Evaporation Rate	Instant
Moisture Content	<10 ppm
Odor	Slight, Ether
Vapor Pressure at 20°C	38 PSIA
Health, Safety and Environmental Data	
Flammable	No
Flashpoint	None
Organic Content (g/L)	0
NFPA	Health: 1 Fire: 3 Instability: 1
RoHS and WEEE Compliant	Yes
Toxicity Rating (ppm, 8hr. TWA, TLV)	1000
GHS / HCS Pictogram	No Pictogram Required, USA Compressed Gas, See SDS
TriggerGrip™ Compatible	No
Aerosol Packaging	12 cans / box
Shelf Life	Unlimited
Recycle	

*Contact MicroCare for specific details

AVAILABILITY: Stocked by MicroCare distributors world-wide. Contact MicroCare for a distributor near you. For more information contact MicroCare directly or visit www.MicroCare.com.

The Dusters containing HFC-134a are not available in the EU, Japan and Australia.