

DO NOT
SCALE FROM
THIS PRINT




TABLE 1 (BOARD TO BOARD)		
STYLE	"A"	
-19	0.75	[19.0]
-25	0.98	[25.0]
-30	1.18	[30.0]

RU8-1XX-XX-XX-XX-DV-XX-X-XX

No OF POSITIONS
-40, -50, & -60

STACK HEIGHT
-19, -25, -30
(SEE TABLE 1)

SIGNAL ROUTING
-SE: SINGLE ENDED
-DP: DIFFERENTIAL PAIRS

CONNECTOR PLATING
SPECIFICATION
(VALUES GIVEN ARE IN MICRO-INCHES)
-SM: SELECTIVE, 30 AU / 50 NI MIN
ON CONTACT, MATTE TIN TAIL
-H: HEAVY GOLD, 30 AU / 50 NI MIN
ON CONTACT, 3 AU / 50 NI MIN ON TAIL
-S: SELECTIVE, 30 AU / 50 NI MIN
ON CONTACT, MATTE TIN TAIL
-L: LIGHT SELECTIVE, 10 AU / 50 NI MIN
ON CONTACT, MATTE TIN TAIL

CONNECTOR PACKAGING
-TR: TAPE & REEL
(LEAVE BLANK FOR TRAYS)

OPTION
-K: POLYAMIDE FILM PAD
(USE K-DOT-.217-.313-.005)

OPTION
-BL: BOARD LOCK
(FIG. 2, SHT. 2)(AVAILABLE
ON -25 & -30 STACK HEIGHTS ONLY)

ROW SPECIFICATION
-DV: DUAL VERTICAL




FIG. 1
RU8-160-19-SE-XX-DV SHOWN

- NOTES:
- 1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
 - 2. BOTH HSEC8 CONNECTORS WILL BE SHIPPED WITH THE SAME OPTIONS EXCEPT FOR -BL OPTION.
 - 3. REFERENCE HSEC8 DRAWING FOR ALL OTHER DIMENSIONS AND OPTIONS.
 - 4. HSEC8 ASSEMBLIES WILL BE TRAY PACKAGED AND HSC8 BOARDS WILL BE PACAGED IN BAGS.

TABLE 2		
No OF POS	"B"	"C"
-40	1.567 [39.80]	2.010 [51.05]
-50	1.882 [47.80]	2.325 [59.05]
-60	2.197 [55.80]	2.640 [67.05]

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1:1

INSULATOR: LCP, UL 94 VO, COLOR: BLACK
CONTACT: BRUSH ALLOY, 390 HT
LATCH ARM: LCP

F:\DWG\MISC\MKTG\RU8-1XX-XX-XX-DV-XX-X-XX-MKT.SLDDRW

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
.8mm BOARD TO BOARD KIT

DWG. NO.
RU8-1XX-XX-XX-XX-DV-XX-X-XX

BY: ELS 8/17/04 SHEET 1 OF 2





TABLE 3	
PART NUMBER	PCB-100256-RU8X-XXX-XX-XX
RU8-140-19-SE-XX-DV-XX	PCB-100256-RU8-040-19-SE
RU8-140-19-DP-XX-DV-XX	PCB-100256-RU8-040-19-DP
RU8-140-25-SE-XX-DV-XX	PCB-100256-RU8-040-25-SE
RU8-140-25-DP-XX-DV-XX	PCB-100256-RU8-040-25-DP
RU8-140-25-SE-XX-DV-BL-XX	PCB-100256-RU8L-040-25-SE
RU8-140-25-DP-XX-DV-BL-XX	PCB-100256-RU8L-040-25-DP
RU8-140-30-SE-XX-DV-XX	PCB-100256-RU8-040-30-SE
RU8-140-30-DP-XX-DV-XX	PCB-100256-RU8-040-30-DP
RU8-140-30-SE-XX-DV-BL-XX	PCB-100256-RU8L-040-30-SE
RU8-140-30-DP-XX-DV-BL-XX	PCB-100256-RU8L-040-30-DP
RU8-150-19-SE-XX-DV-XX	PCB-100256-RU8-050-19-SE
RU8-150-19-DP-XX-DV-XX	PCB-100256-RU8-050-19-DP
RU8-150-25-SE-XX-DV-XX	PCB-100256-RU8-050-25-SE
RU8-150-25-DP-XX-DV-XX	PCB-100256-RU8-050-25-DP
RU8-150-25-SE-XX-DV-BL-XX	PCB-100256-RU8L-050-25-SE
RU8-150-25-DP-XX-DV-BL-XX	PCB-100256-RU8L-050-25-DP
RU8-150-30-SE-XX-DV-XX	PCB-100256-RU8-050-30-SE
RU8-150-30-DP-XX-DV-XX	PCB-100256-RU8-050-30-DP
RU8-150-30-SE-XX-DV-BL-XX	PCB-100256-RU8L-050-30-SE
RU8-150-30-DP-XX-DV-BL-XX	PCB-100256-RU8L-050-30-DP
RU8-160-19-SE-XX-DV-XX	PCB-100256-RU8-060-19-SE
RU8-160-19-DP-XX-DV-XX	PCB-100256-RU8-060-19-DP
RU8-160-25-SE-XX-DV-XX	PCB-100256-RU8-060-25-SE
RU8-160-25-DP-XX-DV-XX	PCB-100256-RU8-060-25-DP
RU8-160-25-SE-XX-DV-BL-XX	PCB-100256-RU8L-060-25-SE
RU8-160-25-DP-XX-DV-BL-XX	PCB-100256-RU8L-060-25-DP
RU8-160-30-SE-XX-DV-XX	PCB-100256-RU8-060-30-SE
RU8-160-30-DP-XX-DV-XX	PCB-100256-RU8-060-30-DP
RU8-160-30-SE-XX-DV-BL-XX	PCB-100256-RU8L-060-30-SE
RU8-160-30-DP-XX-DV-BL-XX	PCB-100256-RU8L-060-30-DP

FIG. 2
RU8-160-25-SE-XX-DV-BL SHOWN
(AVAILABLE IN -25 & -30 STACKER HEIGHTS ONLY)

PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC. DO NOT SCALE DRAWING SHEET SCALE: 2:1		
	520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322	
	DESCRIPTION: .8mm BOARD TO BOARD KIT	
	DWG. NO. RU8-1XX-XX-XX-XX-DV-XX-X-XX	
BY: ELS	8/17/04	SHEET 2 OF 2