

3M™ Link Connector

Cabling work procedures


Components




Work procedure < wire harnessing >

1. Setting cable on cover

- 1) Look for pin numbers on the groove of cover and cable direction.
- 2) Press cable edge onto the insulation cap of cover edge.




- 3) Fold cover into two and insert in cable.
- 4) Fit the latch edge into the hole and secure it.




2. Fix to the body temporarily

Adjust 4 latches of the body to fit the 4 grooves on the cover, and press till the latch engages the 1st step.




3. Squeeze

Use a pair of pliers to secure the cover to the body at the surface and back with notches.




4. Check

Lastly, check if all 4 latches are engaged.




Work procedures < T-split fabrication >

A) Cut the insulation cap base at the edge of cover with a nipper.



B) Check pin numbers of cover slot and cable direction to set the cable.



C) The terminal edge fabrication work sequence is 1-3), 1-4), 2~4).



Customer and Technical Service

Within the U.S.:

Customer Service: 800-225-5373

Technical Support: 512-984-6703

Outside of the U.S.:

For customer service and technical support, please contact your local 3M Electronic Solutions Division representative.

3M is a trademark of 3M Company.

Important Notice

PRODUCT USE: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's application.

Warranty; Limited Remedy; Limited Liability.

3M's product warranty is stated in its Product Literature available upon request. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



**Electronic Solutions Division
Interconnect Products**

6801 River Place Blvd.
Austin, TX 78726-9000
800-225-5373
www.3Mconnector.com

Please recycle. Printed in USA.
© 3M 2010

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[38104-E020-G00FL](#) [38104-F018-F00FL](#) [7010321947](#) [7100227699](#)