

Product Description

3M™ Brown Stripper Pad 7100 is a floor maintenance stripping pad made of nylon and polyester fibers in an open textured, non-woven construction. Abrasive particles are dispersed throughout and bonded to the non-woven construction with a durable resin system that permeates the entire pad. Unique design and durable construction make these pads the industry standard for consistent performance and long life.

- Designed to strip floor finish from floor prior to refinishing
- For use on standard, low speed automatic scrubbers and rotary floor machines (175 - 600 rpm)

Applications

This product is used with water-based floor finish stripping solutions to remove old soiled floor finishes and sealers. The product is also used to clean heavily soiled hard surface floors such as concrete when used with appropriate cleaning chemicals. The product is intended for use on standard, low speed automatic scrubbers and rotary floor machines.

For use on finish-coated flooring such as sheet vinyl, vinyl tile, marble, terrazzo or concrete.

Features and Benefits

Uniform coating throughout every 3M[™] floor pad reduces the number of knots and clumps, which eliminates scratching of floors while providing greater consistency and extended pad life.

Pads are reversible and will not be significantly affected by water, detergents, or cleaners normally used for floor maintenance.

Exacting standards for quality mean thickness uniformity from edge to edge and pad to pad are exceptional, resulting in consistent performance without pad wobble or machine vibration. The precise center-hole placement and roundness of the pads also contributes to the smooth operation which extends pad life and may help reduce operator fatigue.

Packaging and Marking

Each carton shall be labeled to identify the contents by product name, size, quantity and manufacturer. Each pad shall be printed with the manufacturer's name.

Quick Links

<u>Facilities Website</u> Safety Data Sheets (SDS)

Some of these links lead to web-based resources that are not product-specific

Standard Sizes

Circular discs and other shapes are available in a variety of common sizes. Pads are nominally one inch thick.

Pad Use and Cleaning

Dust mop or sweep floors prior to scrubbing with stripping or cleaning solution and floor pad. Pick up dirty solution with a mop, wet vacuum, or automatic scrubber. Rinse floor and let dry prior to recoating or opening to traffic.

Pads may be hosed out using a pressure spray nozzle to remove soil. Pads may be soaked in detergent or diluted stripping solution to dissolve caked soil or finish prior to hosing out.

Storage

Store indoors in original packaging and under normal facility conditions.

Product Characteristics

3M™ Brown Stripper Pad 7100		Test Method
Fiber Type	Nylon/Polyester	N/A
Weight (4 in. by 6 in.)	27.3 g	CCD0015
O.D. Dimension	Designated Size	CCD0004
	±1/16 in.	
Thickness	1 in. nominal	CCD0002
Alkali Resistance (Tensile Retention)	99%	CCD0005,6
Aggressiveness	2.2	CCD0020
Packaging Recycle Content	50-100% recycled content	N/A

Explanation of Signal Word Consequences



DANGER

Indicates a hazardous situation which, if not avoided, will result in serious injury or death.



WARNING

Indicates a hazardous situation which, if not avoided, will result in serious injury or death.





DANGER

To reduce the risks associated with inhalation of or exposure to contaminants:

• DO NOT use this product on any asbestos-containing material.



WARNING

To reduce the risks associated with inhalation of or exposure to contaminants:

- Ensure this product is used in the recommended applications with the suggested equipment.
- Do not allow this product to be used by untrained operators.
- Always follow standard safety practices, including wearing appropriate protective apparel and eye protection, while using this product.

Health and Safety



/!\ CAUTION

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to 3M.com/SDS, or by mail or in case of an emergency, call 1-888-364-3577 or 1-651-737-6501.

When using any equipment, always follow the manufacturers' instructions for safe operation.

Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown should not be used for the purpose of specification limits. If you have questions about this Product, contact the Customer Service Department at 1-800-852-9722.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely

responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty

3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

Limited Remedy

If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



© 3M 2020. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

<u>7000000671</u> <u>7000000672</u> <u>7000045898</u> <u>7000045899</u> <u>7000045900</u> <u>7000045901</u> <u>7000045902</u> <u>7000045903</u> <u>7000120638</u> <u>7000144592</u> <u>7000144593</u>