

3M™ Scotch® Transparent Film Tape 681

Product Description

Scotch® Tape 681 is an excellent high tack, transparent film tape used for various packaging applications such as temporary holding, combining, light-duty carton sealing, bag sealing, and attaching.

Product Features

- Meets CID A-A-1684.
- Moisture and chemical resistant.
- Long aging stability.
- Formulated for easy unwind.
- Can be used in applications where the presence of moisture or chemicals would cause other films to fail.
- Resists turning brittle with age.
- Fade resistant for carbonless images.
- Immediate adhesion to variety of substrates.



3M™ Scotch® Transparent Film Tape 681

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Property	Values		Method
Color	Transparent		
Total Tape Thickness	0.061 mm	2.4 mil	ASTM D3652
Backing Thickness	0.038 mm	1.5 mil	ASTM D3652
Backing	3M™ Paklon™ film		
Adhesive	Pressure sensitive rubber resin		

Typical Performance Characteristics

Property	Values		Method	Substrate
Peel Adhesion	3.3 N/cm	30 oz/in	ASTM D3330	Stainless Steel
Longitudinal Tensile Strength	43.8 N/cm	25 lb/in	ASTM D3759	
Elongation at Break	35 %		ASTM D3759	

Available Sizes

Property	Values	
Standard Roll Length	66 m	72 yd

Table continued on next page

3M™ Scotch® Transparent Film Tape 681

Available Sizes (continued)

Property	Values	
Standard Width	9.5, 12.7, 19, 25.4, 38.1, 50.8, 76.2, 101.6 mm	3/8, 1/2, 3/4, 1, 1.5, 2, 3, 4 in
Core Size (ID)	76.2 mm	3 in
Available Sizes	Custom widths and lengths available on request, subject to minimum order requirements.	

Handling/Application Information

Application Techniques

An extensive line of manual, semi-automatic and automatic equipment is available to facilitate application of Scotch® Tape 681.

Storage and Shelf Life

Storage of Scotch® Tape 681 at 70°F (21°C) and 40-50% relative humidity is recommended. To obtain best performance, use this product within 18 months from date of manufacture.

Industry Specifications

CID A-A-1684

References

- 3m.com Product Page
Url: http://www.3m.com/3M/en_US/company-us/all-3m-products/~//Scotch-Light-Duty-Packaging-Tape-681-Moisture-Chemical-Resistant?N=5002385+3293242204&rt=rud
- Safety Data Sheet
Url: https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=681

3M™ Scotch® Transparent Film Tape 681

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

Important Notice

3M MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. Please remember that many factors can affect the use and performance of a 3M product in a particular application. The materials to be bonded with the product, the surface preparation of those materials, the product selected for use, the conditions in which the product is used, and the time and environmental conditions in which the product is expected to perform are among the many factors that can affect the use and performance of a 3M product. Given the variety of factors that can affect the use and performance of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's application.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/packaging. Address correspondence to: 3M Industrial Adhesives and Tapes Division, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55144-1000. Our fax number is 651-778-4244. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

3M™ Scotch® Transparent Film Tape 681

Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Limitation of Remedies and Liability

If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M shall not otherwise be liable for loss or damages, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including, but not limited to, contract, negligence, warranty, or strict liability.



Industrial Adhesives and Tapes
Division
3M Center
St. Paul, MN 55144-1000
800-362-3550
www.3M.com

Please recycle.
© 3M 2018. All Rights
Reserved.

The brands listed above are trademarks of
3M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[681](#)