



## Technical Data

# 3M™ Doodlebug™ Brown Scrub 'n Strip Pad 8541

### Description

This product is a floor scrubbing pad made of polyester and nylon fibers in an open-web construction. Abrasive particles are dispersed throughout and bonded to the non-woven construction with a durable resin system that permeates the entire pad. The pads are nominally one inch thick and sized to fit standard swivel pad holder.

### Applications

This product is used with detergent solutions to scrub hard surface floors and remove floor finish and wax from hard floor surfaces and baseboards. The pads are designed for use with the swivel pad holder system to reach floor areas not accessible to standard floor machines.

This product fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473

### Features and Benefits

Uniform coating throughout every 3M™ Doodlebug™ pad reduces the number of knots and clumps, which eliminates scratching of floors while providing greater consistency and extended pad life.

Pads are reversible and will not be significantly affected by water, detergents, or cleaners normally used for floor maintenance.

### Packaging and Marking

Each carton shall be labeled to identify the contents by product name, size and manufacturer.

- 5 pads per box
- 4 boxes per case

### Standard Sizes

Pads are nominally one inch thick, 10 inches long and 4-5/8 inches wide.

### Pad Use and Cleaning

Dust mop or sweep floors prior to scrubbing with stripping or cleaning solution and floor pad. Pick up dirty solution with a mop or wet vacuum. Rinse floor and let dry prior to recoating or opening to traffic.

Pads may be hosed out using a pressure spray nozzle to remove soil. Pads may be soaked in detergent or diluted stripping solution to dissolve caked soil or finish prior to hosing out.

### Storage

Store indoors in original packaging and under normal facility conditions.

## Typical Physical Properties and Performance Characteristics

	3M™ Doodlebug™ Brown Scrub 'n Strip Pad 8541	Test Method
Fiber Type	Nylon/Polyester Blend	
Fiber Size	Mixture of Sizes	
Color	Brown	
Weight (4" by 6")	27.3 g	
Thickness	1" Nominal	SB 66
Aggressiveness	2.0 g	SB 3.0
Wear (Weight Loss)	30%	SB 2.0
Packaging Recycle Content	50-100% post-consumer recycled material	

## 3M Branch Sales Offices

### ANCHORAGE

11151 Calaska Circle  
Anchorage, AK 99515

Telephone: 907/522-5200  
Facsimile 907/522-1645

### HONOLULU

4443 Malaai Street  
Honolulu, HI 96818  
Mail to: P.O. Box 30048  
Honolulu, HI 96820

Telephone: 808/422-2721  
Facsimile 808/422-9557

### CONTINENTAL UNITED STATES

Customer Service Department  
3M Center Building 223-5S-07  
St. Paul, MN 55144-1000

Order Entry 1-800-852-9722  
Facsimile 1-800-447-0408

### CANADA

1840 Oxford Street East  
London, Ontario, Canada  
N5V 3G2  
Mail to: P.O. Box 5757  
London, Ontario, Canada  
N6A 4T1

Telephone: 800/364-3577  
Facsimile: 800/479-4453

## Important Notice to User

**Technical Information:** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

**Warranty and Limited Remedy:** 3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



**Building and Commercial  
Services Division**  
St. Paul, MN 55144-1000  
1-800-852-9722  
www.3M.com/facility

3M and Doodlebug are trademarks of  
3M Company.  
Used under license in Canada.  
© 3M 2013. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:  
7000002408