



CMC-0553-8-9CS2351 Product Details

[Share](#) [Print](#) [Email](#)


CMC-0553-8-9CS2351

TE Internal Number: 204193-000

 **Active**

Power Cables

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Modified Fluoropolymer Cable Jacket Material
- High Temperature Application
- Wire Size (AWG/CM) = 6 AWG
- 133 Strands x 29 AWG
- Nominal Outside Diameter = 5.49 mm

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.	Additional Information: • Product Line Information Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Insulation = Double Insulated • Cable Type = Power Electrical Characteristics: • Number of Strands x AWG = 133 Strands x 29 AWG • Voltage Rating (VAC) = 600 Dimensions: • Conductor Outer Diameter (mm [in]) = 4.19 [0.165] Body Features: • Cable Jacket Material = Modified Fluoropolymer • Wire Size (AWG/CM) = 6 AWG • Nominal Outside Diameter (mm [in]) = 5.49 [0.216] • Cable Jacket Color = White • Wire Diameter (mm [in]) = 5.49 [0.216] • Conductor Type = Nickel-Plated Copper • Insulation Material = Radiation-Crosslinked, Modified Flexible ETFE	Configuration Features: • CMA (CMA) = 16,983 • Number of Conductors = 1 Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Operation/Application: • Application = High Temperature Other: • Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

