

# Scotch® Prescription Label Tape 800



## Technical Data

March, 2003

### Product Description

Scotch® Prescription Label Tape 800 is a transparent tape designed for the protection and enhancement of prescription labels. This ultra-clear tape guards the label against abrasion, moisture, and smudging involved with commonly used liquids. It can also be used for attaching, mending, laminating, and clear, easy-open L-clips. Scotch® Tape 800 resists degradation due to sunlight exposure and extended storage, and it is dimensionally stable up to continuous 225°F (107°C). The adhesive resists oozing and has good adherence to most smooth surfaces with an easy unwind.

### Construction

Backing	Adhesive	Colors
Acetate	Acrylic	Clear

### Typical Physical Properties

**Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.**

ASTM Test Method		
Adhesion to Steel:	30 oz./in. width (33 N/100 mm width)	D-3330
Longitudinal Tensile Strength:	12 lbs./in. (210 N/100 mm width)	D-3759
Elongation at Break:	15%	D-3759
Tape Thickness - Backing:	1.6 mil (0.040 mm)	D-3652
Total:	2.5 mil (0.063 mm)	D-3652

### Features

- Protects labels.
- Easy dispensing.
- Low static.
- Clarity.
- Long aging.
- Information won't smudge or rub off.
- Quick and easy in application.
- Handles easily.
- Preserves readability of important information.
- Labels resist puckering, yellowing, and drying out.
- L-clip closures used for preservation of package graphics are easily broken with fingernails for quick opening.

# Scotch® Prescription Label Tape

800

<b>Available Sizes</b>	Standard Widths:	1/2 in., 1 in., 1 1/2 in., 1 3/4 in., and 2 in.
	Available by Special Order:	Custom widths and lengths available on request, subject to minimum order requirements.
	Core Size (ID):	3 in.
	Lengths:	72 yds. (bulk or boxed)

<b>Application Techniques</b>	A line of in-stock manual dispensers is available including the Scotch® Heavy Duty Dispenser C22.
-------------------------------	---

<b>Storage Conditions</b>	Storage of Scotch® Prescription Label Tape 800 at 70°F (21°C) and 40-50% relative humidity is recommended.
---------------------------	--

<b>For Additional Information</b>	To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit <a href="http://www.3M.com/packaging">www.3M.com/packaging</a> . Address correspondence to: 3M Industrial Adhesives and Tapes Division, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55144-1000. Our fax number is 651-778-4244. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.
-----------------------------------	---

<b>Important Notice</b>	3M MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. Please remember that many factors can affect the use and performance of a 3M product in a particular application. The materials to be bonded with the product, the surface preparation of those materials, the product selected for use, the conditions in which the product is used, and the time and environmental conditions in which the product is expected to perform are among the many factors that can affect the use and performance of a 3M product. Given the variety of factors that can affect the use and performance of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's application.
-------------------------	--

<b>Limitation of Remedies and Liability</b>	If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M shall not otherwise be liable for loss or damages, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including, but not limited to, contract, negligence, warranty, or strict liability.
---	---

ISO 9002

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9002 standards.



**Industrial Business**  
**Industrial Adhesives and Tapes Division**  
3M Center, Building 21-1W-10, 900 Bush Avenue  
St. Paul, MN 55144-1000



*Recycled Paper*  
*40% pre-consumer*  
*10% post-consumer*

Printed in U.S.A.  
©3M 2003 70-0710-0264-9 (3/03)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000050041](#) [7000125154](#) [7000125155](#)