

















# 3M™ EPX™ Applicators and Nozzles

|  |   | Replacement Plunger Orders |              |               |             |                    |                    |               | Static Mixing Nozzle Options   |   |
|--|---|----------------------------|--------------|---------------|-------------|--------------------|--------------------|---------------|--|---|
|  |   | 43 mL (2:3)                | 45 mL (10:1) | 48.5 mL (1:1) | 50 mL (2:1) | 200 mL (2:1 & 1:1) | 400 mL (2:1 & 1:1) | 490 mL (10:1) |  |   |
| <b>3M™ Scotch-Weld™ EPX™ Plus II Applicator*</b><br><br>Stock #: 62-9170-9932-7<br>UPC: 00-063806-01001-7<br><br>*Includes 1:1, 2:1 and 10:1 plunger. | <b>1:1/2:1 Shared Plunger</b><br>Stock #: 62-9170-9913-7<br>UPC: 00-063806-01000-0                          |                            | ✓            | ✓             |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Green, 48.5mL/50mL<br>Stock #: 62-9154-9148-4<br>UPC: 0-00-76308-86434-7      | <br>Bulk: 62-9171-9954-9<br>Bulk: 0-00-63806-01003-1   |
|  |   |                            | ✓            | ✓             |             |                    |                    |               | <b>3M™ EPX™ Mixing Nozzle</b><br>Helical White, 48.5mL/50mL<br>Stock #: 62-9178-9151-7<br>UPC: 00-063806-01004-8                   | <br>Bulk: 62-9178-9951-0<br>Bulk: 00-063806-01005-5    |
|  | <b>2:1 Plunger</b><br>Used only for <b>2216 epoxy</b><br>Stock #: 62-9170-9922-8<br>UPC: 0-00-76308-86390-6 | ✓                          |              |               |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Gold, 43mL<br>Stock #: 62-9171-9153-8<br>UPC: 0-00-21200-50008-4              | <br>Bulk: 62-9171-9953-1<br>Bulk: 0-00-21200-50009-1   |
|  | <b>10:1 Plunger</b><br>Stock #: 62-9160-9911-2<br>UPC: 0-00-76308-86391-3                                   | ✓                          |              |               |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical White, 43mL<br>Stock #: 62-9178-9150-9<br>UPC: 0-00-51115-81449-0            | <br>Bulk: 62-9178-9950-2<br>Bulk: 0-00-51115-81467-9   |
| <b>3M™ EPX™ Metal Applicator</b><br><br>Stock #: 62-9740-9935-0<br>UPC: 0-00-21200-21789-0  |   | ✓                          |              |               |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Gold, 43mL<br>Stock #: 62-9171-9153-8<br>UPC: 0-00-21200-50008-4              | <br>Bulk: 62-9171-9953-1<br>Bulk: 0-00-21200-50009-1  |
|  | <b>2:1 Plunger</b><br>Stock #: 62-9744-9930-3<br>UPC: 0-00-21200-82314-5                                    |                            |              |               |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical White, 43mL<br>Stock #: 62-9178-9150-9<br>UPC: 0-00-51115-81449-5            | <br>Bulk: 62-9178-9950-2<br>Bulk: 0-00-51115-81467-9 |
|  |   |                            | ✓            |               |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Green, 43mL/48.5mL<br>Stock #: 62-9154-9148-4<br>UPC: 0-00-76308-86434-7      | <br>Bulk: 62-9171-9954-9<br>Bulk: 0-00-63806-01003-1 |
|  |   |                            | ✓            |               |             |                    |                    |               | <b>3M™ EPX™ Mixing Nozzle</b><br>Helical White, 48.5mL/50mL<br>Stock #: 62-9178-9151-7<br>UPC: 00-063806-01004-8                   | <br>Bulk: 62-9178-9951-0<br>Bulk: 00-063806-01005-5  |
| <b>3M™ EPX™ Pneumatic Applicator 48.5/50 mL</b><br><br>Stock #: 62-9781-9931-3<br>UPC: 00-063806-01006-2  | N/A   |                            | ✓            | ✓             |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Green, 43mL/48.5mL<br>Stock #: 62-9154-9148-4<br>UPC: 0-00-76308-86434-7      | <br>Bulk: 62-9171-9954-9<br>Bulk: 0-00-63806-01003-1 |
|  |   |                            | ✓            | ✓             |             |                    |                    |               | <b>3M™ EPX™ Mixing Nozzle</b><br>Helical White, 48.5mL/50mL<br>Stock #: 62-9178-9151-7<br>UPC: 00-063806-01004-8                   | <br>Bulk: 62-9178-9951-0<br>Bulk: 00-063806-01005-5  |
| <b>3M™ Scotch-Weld™ EPX™ Manual Applicator 200 mL</b><br><br>Stock #: 62-9136-9930-2<br>UPC: 0-00-21200-87977-7                                     | <b>1:1/2:1 Shared Plunger</b><br>Stock #: 62-9136-9938-5<br>UPC: 0-00-21200-87981-4                         |                            |              |               | ✓           | ✓                  |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Gold, 200mL and 400mL<br>Stock #: 62-9176-9127-1<br>UPC: 0-00-21200-97331-4   | <br>Bulk: 62-9176-9127-1<br>Bulk: 0-00-21200-97331-4 |
|  |   |                            |              |               |             |                    |                    |               | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical White, 200mL and 400mL<br>Stock #: 62-9142-9930-0<br>UPC: 0-00-21200-87982-1 | <br>Bulk: 62-9142-9930-0<br>Bulk: 0-00-21200-87982-1 |

# 3M™ EPX™ Applicators and Nozzles

|  |     | Replacement Plunger Orders   |              |             |                    |                    |   | Static Mixing Nozzle Options   |  |
|--|-----|--|--------------|-------------|--------------------|--------------------|---|--|--|
|  |     | 37 mL (2:1) & 43 mL (2:3)  | 45 mL (10:1) | 50 mL (1:1) | 200 mL (2:1 & 1:1) | 400 mL (2:1 & 1:1) | 490 mL (10:1)   |  |  |
| <b>3M™ EPX™ 200, 400 mL Manual Applicator</b><br><br><b>Stock #:</b> 62-9148-9930-7<br><b>UPC:</b> 0-00-51111-98073-6             | N/A |  |              |             | ✓                  | ✓                  | ✓   | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Gold, 200mL and 400mL<br><b>Stock #:</b> 62-9176-9127-1<br><b>UPC:</b> 0-00-21200-97331-4    |  |
|  |     | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical White, 200mL and 400mL<br><b>Stock #:</b> 62-9142-9930-0<br><b>UPC:</b> 0-00-21200-87982-1    |              |             |                    |                    |   |  |  |
| <b>3M™ EPX™ 490 mL Manual Applicator</b><br><br><b>Stock #:</b> 62-9182-9930-6<br><b>UPC:</b> 0-00-51115-71115-2                  | N/A |  |              |             |                    |                    | ✓   | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical Orange, 490mL<br><b>Stock #:</b> 62-9158-9136-0<br><b>UPC:</b> 0-00-51115-69042-6           |  |
|  |     | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Green, 490mL<br><b>Stock #:</b> 62-9184-9490-7<br><b>UPC:</b> 0-00-51115-81619-2               |              |             |                    |                    |   |  |  |
| <b>3M™ Scotch-Weld™ EPX™ Pneumatic Applicator 200 mL</b><br><br><b>Stock #:</b> 62-9140-9930-4<br><b>UPC:</b> 0-00-21200-87978-4 | N/A |  |              | ✓           |                    |                    |   | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Gold, 200mL and 400mL<br><b>Stock #:</b> 62-9176-9127-1<br><b>UPC:</b> 0-00-21200-97331-4    |  |
|  |     | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical White, 200mL and 400mL<br><b>Stock #:</b> 62-9142-9930-0<br><b>UPC:</b> 0-00-21200-87982-1  |              |             |                    |                    |   |  |  |
| <b>3M™ EPX™ 400 mL Pneumatic Applicator</b><br><br><b>Stock #:</b> 62-9145-9930-3<br><b>UPC:</b> 0-00-21200-87979-1             | N/A |  |              |             |                    | ✓                  |   | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Gold, 200mL and 400mL<br><b>Stock #:</b> 62-9176-9127-1<br><b>UPC:</b> 0-00-21200-97331-4  |  |
|  |     | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical White, 200mL and 400mL<br><b>Stock #:</b> 62-9142-9930-0<br><b>UPC:</b> 0-00-21200-87982-1  |              |             |                    |                    |   |  |  |
| <b>3M™ EPX™ 490 mL Pneumatic Applicator</b><br><br><b>Stock #:</b> 62-9152-9930-9<br><b>UPC:</b> 0-00-51115-69041-9             | N/A |  |              |             |                    |                    | ✓   | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Helical Orange, 490 mL<br><b>Stock #:</b> 62-9158-9136-0<br><b>UPC:</b> 0-00-51115-69042-6        |  |
|  |     | <b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b><br>Square Green, 490 mL<br><b>Stock #:</b> 62-9184-9490-7<br><b>UPC:</b> 0-00-51115-81619-2            |              |             |                    |                    |   |  |  |
| <b>Standard Caulk Gun</b>  | N/A |  |              |             |                    |                    | <b>3M™ Concrete Repair Urethane 8.4 oz cartridges</b> | <b>3M™ Concrete Repair 8.4 oz Cartridge Nozzles</b><br><b>Stock #:</b> 62-9637-9935-8<br><b>UPC:</b> 0-00-48011-53382-7                         |  |

For low volume applications and take-it-to-the-job convenience, the 3M™ EPX™ Plus II and EPX™ metal manual applicators comfortably dispense any of the 3M™ Scotch-Weld™ Duo-Pak Structural Adhesives. For higher volume applications, select the 200mL manual dispenser, or the 200mL or 400mL pneumatic dispenser. For concrete repair, there are both manual or pneumatic options.

3M™ Scotch-Weld™ One-Part Heat Cured Epoxies require a unique manual or pneumatic dispenser, such as Semco® 250, 350, 850, 950, or equivalent.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[9742](#)