

Technical Data

Scotchgard™ Pretreatment Cleaner Concentrate

Description

Scotchgard™ Pretreatment Cleaner is a concentrated product formulated to loosen and suspend soil to allow heavy soil to be removed during carpet extraction.

Scotchgard™ Pretreatment Cleaner is formulated for use with Scotchgard™ Carpet Protector and is an important part of the 3M carpet care system.

Special Features

- Heavy-duty formula
- Low-foaming formula
- No sticky residue to cause re-soiling

Applications

- Commercial and residential carpets
- Most carpet fibers (nylon, polyester, olefins, wool and blends)
- Most carpet styles (loop or cut piles)
- Safe for use on stain-resistant nylon fibers

Packaging

4 1-gallon bottles per case

General Use Directions

Note:

Test the cleaner in an inconspicuous area to assure the carpet is colorfast. Apply ready-to-use solution to a small area. After several minutes, blot the carpet with a clean white cloth or paper towel. If color from the carpet transfers to the cloth or towel, discontinue use.

1. Vacuum the carpet area thoroughly.
2. Mix 1 part cleaning pretreatment concentrate to 8 parts water (16 ounces per gallon).
3. Add the ready-to-use pretreatment concentrate to a 3M™ All-Purpose Sprayer (Model AP-1) or a bulk pressurized sprayer.
4. Fill the carpet extractor with warm to hot water.
5. Spray the pretreatment cleaner to the carpet area at a rate of 200 ft. per diluted gallon.
6. Allow 1-3 minutes dwell time.
7. Provide agitation to heavily soiled areas using a brush or 3M™ Carpet Bonnet Pad (optional).
8. Extract the carpet using overlapping passes of the extraction wand.
9. Move the extractor slowly over the carpet, making two passes.
10. Dispense rinse water throughout the first pass.

11. On the 2nd pass, vacuum only – do not apply additional water.
12. Apply Scotchgard™ Carpet and Upholstery Protector Concentrate to carpet immediately following extraction cleaning.

NOTE:

Refer to product Material Safety Data Sheets (MSDS: 21-3979-8) for specific health hazard, first aid and precautionary information.

3M Branch Sales Offices

ANCHORAGE

11151 Calaska Circle
Anchorage, AK 99515

Telephone: 907/522-5200
Facsimile 907/522-1645

HONOLULU

4443 Malaai Street
Honolulu, HI 96818
Mail to: P.O. Box 30048
Honolulu, HI 96820

Telephone: 808/422-2721
Facsimile 808/422-9557

CONTINENTAL UNITED STATES

Customer Service Department
3M Center Building 223-5S-07
St. Paul, MN 55144-1000

Order Entry 1-800-852-9722
Facsimile 1-800-447-0408

CANADA

1840 Oxford Street East
London, Ontario, Canada
N5V 3G2
Mail to: P.O. Box 5757
London, Ontario, Canada
N6A 4T1

Telephone: 800/364-3577
Facsimile: 800/479-4453

Important Notice to User

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



Building and Commercial Services Division

St. Paul, MN 55144-1000
1-800-852-9722
www.3M.com/building

3M and Scotchgard are trademarks of 3M Company.
Used under license in Canada.
© 3M 2012. All rights reserved.
Asset ID 60194

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7100122464](#)