

SPEC# \_\_\_\_\_

QUANTITY \_\_\_\_\_

application: **DROP-IN REPLACEMENTS**



models:  
**20” Cartridges**

The 3M line of drop-in cartridges for plastic and isoplast housings are an economical way to help reduce constituents in water that can cause equipment damage and unappealing product. Media choices of graded porosity, charge modified and activated carbon provide a wide range of particulate holding capacities, chlorine reduction capabilities and micron ratings. These cartridges can be used as retrofits in 20” housings to upgrade current filtration.

**PRODUCT SPECIFICATIONS**

Model Number	Part Number	Micron Rating	Claims	Flow Rate gpm (lpm)	Type
CFS8504-C20	55847-09	10	Particulate Reduction	12 (45.4)	Uniform Porosity
CFS110-C20	55591-05	5	Particulate Reduction	12 (45.4)	Progressive Porosity
CFS124-C20	55595-04	25	Course Particulate Reduction	12 (45.4)	Progressive Porosity
CFS017-C20	55593-05	5	Chlorine Taste and Odor Reduction	6 (22.7)	Granular Activated Carbon
CFS017S-C20	55594-08	5	Chlorine Taste and Odor Reduction, Scale Inhibition	6 (22.7)	Granular Activated Carbon
20” Carbon Block	55907-01	10	Chlorine Taste and Odor Reduction	6 (22.7)	Carbon Block
CFSCB05S-C20	FCBB20S	5	Chlorine Taste and Odor, Scale Inhibitor	4 (15.1)	Carbon Block

# 20" Cartridges

SPEC# \_\_\_\_\_  
QUANTITY \_\_\_\_\_  
MODEL NUMBER \_\_\_\_\_  
PART NUMBER \_\_\_\_\_

# 3M™ Water Filtration Products

## IMPORTANT: INSTALLATION TIPS

These installation tips are for informational purposes only and are not intended to be used as actual installation instructions. **CAUTION:** To reduce the risk associated with property damage due to water leakage:

- **Read and follow** Use Instructions before installation and use of this system.
- Installation and use **MUST** comply with all state and local plumbing codes.
- **Protect from freezing**, remove filter cartridge when temperatures are expected to drop below 40°F (4.4°C).
- **Do not install on hot water supply lines.** The maximum operating water temperature of this filter system is 100°F (37.8°C).
- **Do not install** where water hammer conditions may occur. If water hammer conditions exist you must install a water hammer arrester. Contact a plumbing professional if you are uncertain how to check for this condition.
- The disposable filter cartridge **MUST** be replaced every 12 months, at the rated capacity or if a noticeable reduction in flow rate occurs.

**⚠ WARNING:** To reduce the risk associated with the ingestion of contaminants:

- **Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.**

3M Purification Inc. recommends regularly scheduled maintenance and replacement of the filter cartridge(s) in order for the product to perform as advertised/sold. 3M Purification Inc. shall not be liable for system failures due to improper maintenance.

## LIMITED WARRANTY

3M Purification Inc. warrants 20" Cartridges only to be free from defects in material and workmanship for five (5) years from the date of purchase. This warranty does not cover failures resulting from abuse, misuse, alterations or damage not caused by 3M Purification Inc. or failure to follow installation and use instructions. No warranty is given as to the service life of any filter cartridge or membrane as it will vary with local water conditions and consumption. **3M PURIFICATION INC. MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOMER OR USAGE OF TRADE.** If the Product fails to satisfy this Limited Warranty during the warranty period, 3M Purification Inc., at its option, will replace the Product or refund your Product purchase price. This warranty does not cover labor. **The remedy stated in this paragraph is Customer's sole remedy and 3M Purification Inc.'s exclusive obligation. For additional information, see the entire Limited Warranty located in the product Installation and Operation Instruction Manual.**

**Limitation of Liability:** 3M Purification Inc. will not be liable for any loss or damage arising from this 3M Purification Inc. product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states and countries do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.



**3M Purification Inc.**  
400 Research Parkway  
Meriden, CT 06450 U.S.A.  
Toll Free: 866.990.9785  
Worldwide: 203.237.5541  
Fax: 203.238.8701  
www.3Mfoodservice.com  
www.3Mpurification.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7100005623](#) [7100061003](#)