



Technical Data

3M™ Doodlebug™ Blue Scrub Pad 8242

Description

This product is a floor maintenance scrubbing pad made of polyester and nylon fibers in an open-web construction. Abrasive particles are dispersed throughout and bonded to the non-woven construction with a durable resin system that permeates the entire pad. The pads are nominally one inch thick and sized to fit standard swivel pad holder.

Applications

This product is used with water or detergent solutions for cleaning and medium-duty scrubbing of hard surface floors, baseboards and stairs. The pads are designed for use with the swivel pad holder system to reach floor areas not accessible to standard floor machines.

This product fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473

Features and Benefits

Uniform coating throughout every 3M™ Doodlebug™ pad reduces the number of knots and clumps, which eliminates scratching of floors while providing greater consistency and extended pad life.

Pads are reversible and will not be significantly affected by water, detergents, or cleaners normally used for floor maintenance.

Packaging and Marking

Each carton shall be labeled to identify the contents by product name, size and manufacturer.

- 5 pads per box
- 4 boxes per case

Standard Sizes

Pads are nominally one inch thick, 10 inches long and 4-5/8 inches wide.

Pad Use and Cleaning

Dust mop or sweep floors prior to scrubbing. Pick up dirty solution with a mop or wet vacuum. Rinse floor and let dry prior to recoating or opening to traffic.

Pads may be hosed out using a pressure spray nozzle to remove soil. Pads may be soaked in detergent or diluted stripping solution to dissolve caked soil or finish prior to hosing out.

Storage

Store indoors in original packaging and under normal facility conditions.

Typical Physical Properties and Performance Characteristics

	3M™ Doodlebug™ Blue Scrub Pad 8242	Test Method
Fiber Type	Nylon/Polyester Blend	
Fiber Size	Mixture of Sizes	
Color	Blue	
Weight (4" by 6")	21.2 g	
Thickness	1" Nominal	SB 66
Aggressiveness	1.2 g	SB 3.0
Wear (Weight Loss)	10%	SB 2.0
Packaging Recycle Content	50-100% post-consumer recycled material	

3M Branch Sales Offices

ANCHORAGE

11151 Calaska Circle
Anchorage, AK 99515

Telephone: 907/522-5200
Facsimile 907/522-1645

HONOLULU

4443 Malaai Street
Honolulu, HI 96818
Mail to: P.O. Box 30048
Honolulu, HI 96820

Telephone: 808/422-2721
Facsimile 808/422-9557

CONTINENTAL UNITED STATES

Customer Service Department
3M Center Building 223-5S-07
St. Paul, MN 55144-1000

Order Entry 1-800-852-9722
Facsimile 1-800-447-0408

CANADA

1840 Oxford Street East
London, Ontario, Canada
N5V 3G2
Mail to: P.O. Box 5757
London, Ontario, Canada
N6A 4T1

Telephone: 800/364-3577
Facsimile: 800/479-4453

Important Notice to User

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



**Building and Commercial
Services Division**
St. Paul, MN 55144-1000
1-800-852-9722
www.3M.com/facility

3M and Doodlebug are trademarks of
3M Company.
Used under license in Canada.
© 3M 2013. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:
7000002234