

3M™ Cable Accessory

Drain Wire Spring Clip



3535 Series



- **Drain Wire Spring Clips** are used to attach a drain wire to the shield of a round cable. The drain wire can then be routed to a metal cabinet or through the connector body to the inside of the cabinet.
- One size spring clip fits all sizes of cable; 9-64 conductor, while providing the same force for each cable diameter.
- We recommend covering the termination area with adhesive lined 3M™ Heat Shrink Tubing EPS-300 for improved physical, electrical and visual properties.
- RoHS* compliant

Date Modified: February 15, 2005

TS-0269-09
Sheet 1 of 1



Notes:

1. Material: Stainless Steel, .0025 [0.064] thick.
2. Uncoiled length is 4.5 [114.3].

Inch
[mm]

Tolerance Unless Noted			
	.0	.00	.000
inch	±.1	±.01	±.005

[] Dimensions for Reference
Only

Ordering Information

3535-0000

Note: Packaged 100 per bag.

*RoHS = Directive 2002/95/EC,
Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment



Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.
For technical, sales or ordering information call

800-225-5373

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 1 year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronic Solutions Division

6801 River Place Blvd.
Austin, TX 78726-9000
www.3M.com/esd



Minimum 10%
Post-consumer Fiber

Printed in USA.

© 3M 2005

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[3535-0000](#)