





3M™ Label Holder SOR E8 - SOR E10

The 3M™ Label Holders SOR E8 and SOR E10 provide wire identification (A or B for each wire position) and numbering (1 to 8 or 1 to 10) for the 3M™ High Density Cross-Connect Module STG and STR Series.

SOR E label holders require one module position on a back mount frame but maintain the high-density pitch of the STG and STR cross-connect modules. They can be easily snapped on or removed from the supporting back mount frame without any special tool.

Specifications

Dimensions (10 pairs - 11 positions)	Materials
Length SOR E8: 126 mm / 4.96 in.	Label holder body: UL 94 V-0 Polycarbonate
Length SOR E10: 146 mm / 5.78 in.	
Height: 51 mm / 2.00 in.	
Width: 14 mm / 0.55 in.	



3M™ Label Holders SOR E8 and SOR E10



3M™ Label Holder SOR E10 on 3M™ High Density Cross-Connect Back Mount Frame STG2000

Ordering Information

Model Number	Description	3M ID	Minimum Order
C220673B	SOR E8 8-Pair Label Holder	FQ100004057	20
C220674B	SOR E10 10-Pair Label Holder	FQ100004065	20

Compliant with EU RoHS Directive (2005/95/EC)

"RoHS Compliant 2005/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2005/618/EC, unless the substance is in an application that is exempt under RoHS. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether indirect, special, incidental or consequential regardless of the legal theory asserted.**



Communication Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800/426 8688
Fax 800/626 0329
www.3M.com/Telecom

Please recycle. Printed in USA.
© 3M 2011. All rights reserved.
80-6113-8613-9

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[C220674B](#)