





























# 3M™ EPX™ Applicators and Nozzles

		Replacement Plunger Orders						Nozzle Length (Inches)		Static Mixing Nozzle Options	
		43 mL (2:3)	45 mL (10:1)	48.5 mL (1:1)	50 mL (2:1)	200 mL (2:1 & 1:1)	400 mL (2:1 & 1:1)				
<b>3M™ Scotch-Weld™ EPX™ Plus II Applicator*</b> Stock #: 7100148764 UPC: 00-063806-01001-7 	<b>1:1/2:1 Shared Plunger</b> Stock #: 7010415317 UPC: 00-063806-01000-0		✓	✓				3.6	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Green, 48.5mL/50mL Stock #: 7100104991 UPC: 0-00-76308-86434-7	 Bulk: 7100148765 Bulk: 0-00-63806-01003-1	
			✓	✓				6.2	<b>3M™ EPX™ Mixing Nozzle</b> Helical White, 48.5mL/50mL Stock #: 7100148766 UPC: 00-063806-01004-8	 Bulk: 7100148756 Bulk: 00-063806-01005-5	
	<b>2:1 Plunger</b> Used only for <b>2216 epoxy</b> Stock #: 7010309947 UPC: 0-00-76308-86390-6	✓							3.3	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Gold, 43mL Stock #: 7000000952 UPC: 0-00-21200-50008-4	 Bulk: 7000121587 Bulk: 0-00-21200-50009-1
	<b>10:1 Plunger</b> Stock #: 7010329933 UPC: 0-00-76308-86391-3		✓						5.8	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Helical White, 43mL Stock #: 7100034271 UPC: 0-00-51115-81449-0	 Bulk: 7100034272 Bulk: 0-00-51115-81467-9
*Includes 1:1, 2:1 and 10:1 plunger.								3.6	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Orange, 45mL Stock #: 7100007806 UPC: 0-00-51115-89043-3		
<b>3M™ EPX™ Metal Applicator</b> Stock #: 7000000954 UPC: 0-00-21200-21789-0 	<b>2:1 Plunger</b> Stock #: 7000000956 UPC: 0-00-21200-82314-5	✓						3.3	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Gold, 43mL Stock #: 7000000952 UPC: 0-00-21200-50008-4	 Bulk: 7000121587 Bulk: 0-00-21200-50009-1	
								5.8	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Helical White, 43mL Stock #: 7100034271 UPC: 0-00-51115-81449-5	 Bulk: 7100034272 Bulk: 0-00-51115-81467-9	
				✓				3.6	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Green, 43mL/48.5mL Stock #: 7100104991 UPC: 0-00-76308-86434-7	 Bulk: 7100148765 Bulk: 0-00-63806-01003-1	
				✓				6.2	<b>3M™ EPX™ Mixing Nozzle</b> Helical White, 48.5mL/50mL Stock #: 7100148766 UPC: 00-063806-01004-8	 Bulk: 7100148756 Bulk: 00-063806-01005-5	
<b>3M™ EPX™ Pneumatic Applicator 48.5/50 mL</b> Stock #: 7100148769 UPC: 00-063806-01006-2 	N/A		✓	✓				3.6	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Green, 43mL/48.5mL Stock #: 7100104991 UPC: 0-00-76308-86434-7	 Bulk: 7100148765 Bulk: 0-00-63806-01003-1	
			✓	✓				6.2	<b>3M™ EPX™ Mixing Nozzle</b> Helical White, 48.5mL/50mL Stock #: 7100148766 UPC: 00-063806-01004-8	 Bulk: 7100148756 Bulk: 00-063806-01005-5	
<b>3M™ Scotch-Weld™ EPX™ Manual Applicator 200 mL</b> Stock #: 7000046632 UPC: 0-00-21200-87977-7 	<b>1:1/2:1 Shared Plunger</b> Stock #: 7000121583 UPC: 0-00-21200-87981-4					✓	✓	5.0	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Gold, 200mL and 400mL Stock #: 7000028616 UPC: 0-00-21200-97331-4		
								7.5	<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Helical White, 200mL and 400mL Stock #: 7000046633 UPC: 0-00-21200-87982-1		

# 3M™ EPX™ Applicators and Nozzles

	Replacement Plunger Orders	37 mL (2:1) & 43 mL (2:3)					45 mL (10:1)		50 mL (1:1)		200 mL (2:1 & 1:1)		400 mL (2:1 & 1:1)		Nozzle Length (Inches)	Static Mixing Nozzle Options
<b>3M™ EPX™ 200, 400 mL Manual Applicator</b>    <b>Stock #:</b> 7000046634  <b>UPC:</b> 0-00-51111-98073-6	N/A															<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Gold, 200mL and 400mL <b>Stock #:</b> 7000028616 <b>UPC:</b> 0-00-21200-97331-4 
<b>3M™ EPX™ 490 mL Manual Applicator</b>    <b>Stock #:</b> 7100015958  <b>UPC:</b> 0-00-51115-71115-2	N/A															<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Helical Orange, 490mL <b>Stock #:</b> 7100015959 <b>UPC:</b> 0-00-51115-69042-6 
<b>3M™ Scotch-Weld™ EPX™ Pneumatic Applicator 200 mL</b>    <b>Stock #:</b> 7000121584  <b>UPC:</b> 0-00-21200-87978-4	N/A															<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Gold, 200mL and 400mL <b>Stock #:</b> 7000028616 <b>UPC:</b> 0-00-21200-97331-4 
<b>3M™ EPX™ 400 mL Pneumatic Applicator</b>    <b>Stock #:</b> 7000148285  <b>UPC:</b> 0-00-21200-87979-1	N/A															<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Square Gold, 200mL and 400mL <b>Stock #:</b> 7000028616 <b>UPC:</b> 0-00-21200-97331-4 
<b>3M™ EPX™ 490 mL Pneumatic Applicator</b>    <b>Stock #:</b> 7100011053  <b>UPC:</b> 0-00-51115-69041-9	N/A															<b>3M™ Scotch-Weld™ EPX™ Mixing Nozzle</b> Helical Orange, 490 mL <b>Stock #:</b> 7100015959 <b>UPC:</b> 0-00-51115-69042-6 
<b>Standard Caulk Gun</b>	N/A															<b>3M™ Concrete Repair 8.4 oz Cartridge Nozzles</b> <b>Stock #:</b> 7000046642 <b>UPC:</b> 0-00-48011-53382-7 

For low volume applications and take-it-to-the-job convenience, the 3M™ EPX™ Plus II and EPX™ metal manual applicators comfortably dispense any of the 3M™ Scotch-Weld™ Duo-Pak Structural Adhesives. For higher volume applications, select the 200mL manual dispenser, or the 200mL or 400mL pneumatic dispenser. For concrete repair, there are both manual or pneumatic options.

3M™ Scotch-Weld™ One-Part Heat Cured Epoxies require a unique manual or pneumatic dispenser, such as Semco® 250, 350, 850, 950, or equivalent.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[EPX-PLUNGER](#)