


## 2-POLE HOUSINGS


### 50 Amp HOUSINGS



OPERATING TEMPERATURE RANGE: -20°C ~ +125°C  
MAXIMUM ELECTRICAL RATING: 600 VOLTS MAX.  
HOUSING MATERIAL: POLYCARBONATE(PC)  
SPRING MATERIAL: STAINLESS STEEL

| ITEM NO.     | DIMENSION <small>inch<br/>mm</small> |               |              | DESCRIPTION   | COLOR  |  | Q'TY<br>BOX |
|--------------|--------------------------------------|---------------|--------------|---|--------|--|-------------|
|              | W                                    | L             | H            |   |        |  |             |
| BMC2S-RED    | 1.374<br>34.9                        | 1.890<br>48.0 | .626<br>15.9 | HOUSING WITH<br>TWO SPRINGS,<br>CAN BE USED<br>WITH<br>50Amp SERIES<br>CONTACTS | RED    |  | 25          |
| BMC2S-GREY   |                                      |               |              |   | GREY   |  | 25          |
| BMC2S-BLACK  |                                      |               |              |   | BLACK  |  | 25          |
| BMC2S-BLUE   |                                      |               |              |   | BLUE   |  | 25          |
| BMC2S-GREEN  |                                      |               |              |   | GREEN  |  | 25          |
| BMC2S-ORANGE |                                      |               |              |   | ORANGE |  | 25          |
| BMC2S-YELLOW |                                      |               |              |   | YELLOW |  | 25          |

## 120 Amp HOUSINGS



OPERATING TEMPERATURE RANGE: -20°C ~ +125°C  
MAXIMUM ELECTRICAL RATING: 600 VOLTS MAX.  
HOUSING MATERIAL: POLYCARBONATE(PC)  
SPRING MATERIAL: STAINLESS STEEL

| ITEM NO.    | HOUSING<br>COLOR | DIMENSION <small>inch<br/>mm</small> |               |              | DESCRIPTION  | COLOR |  | Q'TY<br>BOX |
|-------------|------------------|--------------------------------------|---------------|--------------|--|-------|--|-------------|
|             |                  | W                                    | L             | H            |  |       |  |             |
| BMC2MS-RED  | RED              | 1.748<br>44.4                        | 2.50<br>63.51 | .803<br>20.4 | HOUSING WITH<br>TWO SPRINGS,<br>CAN BE USED<br>WITH<br>120Amp SERIES<br>CONTACTS | RED   |  | 10          |
| BMC2MS-GREY | GREY             |                                      |               |              |  | GREY  |  | 10          |
| BMC2MS-BLUE | BLUE             |                                      |               |              |  | BLUE  |  | 10          |



ALL LISTED

⊙ : NOT RU AND C-RU LISTED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[BMC2S-GREY](#)