


VINYL-INSULATED (EASY ENTRY) LOCKING SPADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL
INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	LSVEB1-3.2	LSVE1-3.2	#4	.126 3.2	.252 6.4	.256 6.5	.874 22.2	.441 11.2	.157 4.0	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
	LSVEB1-3.7	LSVE1-3.7	#6	.146 3.7									1000
	LSVEBS1-4	LSVES1-4	#8	.169 4.3	.283 7.2								1000
	LSVEBL1-4	LSVEL1-4	#8	.169 4.3	.319 8.1								1000
	LSVEBS1-5	LSVES1-5	#10	.209 5.3									1000
	LSVEBL1-5	LSVEL1-5	#10	.209 5.3	.374 9.5								1000
16-14 A.W.G. 1.5-2.5 mm ²	LSVEB2-3.2	LSVE2-3.2	#6	.146 3.7	.236 6.0	.256 6.5	.886 22.5	.453 11.5	.177 4.5	.091 2.3	.031 0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
	LSVEB2-3.7	LSVE2-3.7	#6	.146 3.7									1000
	LSVEBL2-3.7	LSVEL2-3.7	#6	.146 3.7	.283 7.2								1000
	LSVEB2-4	LSVE2-4	#8	.169 4.3									1000
	LSVEBL2-4	LSVEL2-4	#8	.169 4.3	.319 8.1								1000
	LSVEBS2-5	LSVES2-5	#10	.209 5.3									1000
	LSVEBL2-5	LSVEL2-5	#10	.209 5.3	.366 9.3								1000
	LSVEB2-6	LSVE2-6	1/4	.252 6.4									1000
12-10 A.W.G. 4-6 mm ²	LSVEBS5-3.7	LSVES5-3.7	#6	.146 3.7	.307 7.8	.276 7.0	1.035 26.3	.555 14.1	.248 6.3	.134 3.4	.039 1.0	IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500
	LSVEB5-3.7	LSVE5-3.7	#6	.146 3.7	.327 8.3								500
	LSVEB5-4	LSVE5-4	#8	.169 4.3									500
	LSVEB5-5	LSVE5-5	#10	.209 5.3	.354 9.0	.472 12.0	1.283 32.6						500
	LSVEB5-6	LSVE5-6	1/4	.252 6.4	.472 12.0								500

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[LSVE1-3.7](#) [LSVE2-3.7](#) [LSVE5-3.7](#) [LSVE5-4](#) [LSVE5-5](#) [LSVE5-6](#) [LSVEL1-5](#) [LSVEL2-5](#) [LSVES1-4](#)