



High Performance

# Hot Glue Guns



17620  
Glue Gun 25W  
w/Travel Case



17621  
Glue Gun 60W  
w/Travel Case



17610  
Glue Gun 60W  
w/Long Trigger

Glue Gun 25W	
item #	17620
Power	25W
Power Cabel Length	4'
Package Contents	<ul style="list-style-type: none"><li>• Glue Gun 25W</li><li>• Durable Plastic Travel Case</li><li>• 6 Glue Sticks</li></ul>

Glue Gun 60W	
item #	17621
Power	60W
Power Cabel Length	4'
Package Contents	<ul style="list-style-type: none"><li>• Glue Gun 60W</li><li>• Durable Plastic Travel Case</li><li>• 6 Glue Sticks</li></ul>

Glue Gun 60W w/ Long Trigger	
item #	17610
Power	60W
Power Cabel Length	4'
Package Contents	<ul style="list-style-type: none"><li>• Glue Gun 60W w/Long Trigger</li><li>• 2 Glue Sticks</li></ul>

## Designed for professional bonding

Aven's hot glue guns are designed for professional bonding, DIY home repairs, wood work, and hobbies. The glue heats up quickly for easy application.

Items 17620 and 17621 include a handy travel and storage case with built-in slots for 6 glue sticks.

Item 17610 features a long trigger, providing smooth glue-flow, easing hand fatigue over repeated use.

## FEATURES

- Ergonomic hand grips
- Easy reach trigger
- Narrow nozzle for precise glue application
- Flip-out stand
- Heats up quickly
- 4' power cable

**Also Available:**  
11.8" Glue Stick 35 Pack



Item# 17615



### **17620 Hot Glue Gun 25W with Plastic Travel Case**

- Ergonomic hand grip
- Easy reach trigger
- Flip-out stand
- Heats up quickly
- Narrow nozzle for precise glue application
- 4' power cable
- Power Consumption: 25W (100-240V)
- Durable travel case with 6 glue sticks



### **17621 Hot Glue Gun 60W with Plastic Travel Case**

- Ergonomic hand grip
- Easy reach trigger
- Temperature dial (180°-240° C)
- Flip-out stand
- Heats up quickly
- Narrow nozzle for precise glue application
- 4' power cable
- Power Consumption: 60W (100-240V)
- Durable travel case with 6 glue sticks



### **17610 Long Trigger Hot Glue Gun**

- Ergonomic hand grip
- Long trigger for improved glue flow
- On/off switch
- Flip-out stand with recessed area for collecting excess glue
- Heats up quickly
- Narrow nozzle for precise glue application
- 4' power cable
- Power Consumption: 60W (100-240V)
- Includes 2 glue sticks

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aven:](#)

[17610](#) [17615](#) [17620](#) [17621](#)