

MultiTask Surface Electronics Cleaner Presaturated Wipes MultiClean[™]



- Removes solder paste, flux residues, finger prints, uncured epoxy residues, light oils and grease
- 70% High Purity Isopropyl Alcohol (IPA) and 30% Deionized Water saturated lint-free wipes
- ESD-safe
- · No rip heavy-duty wipe
- Unlimited shelf-life

Product Information

The MultiTask Surface Electronic Cleaner - *MultiClean* Presaturated Wipes provide fast and safe cleaning in almost any production environment. Using a strong, shred-proof, disposable wipe saturated with high purity isopropyl alcohol and deionized water, it is well suited for cleaning medical devices, electronics, stencils, work benches, tools, production machinery, and any surface that requires hygienic grade cleaning.

Versatile, it cleans most solder pastes found on SMT stencils. It also cleans organic and ionic residues, light oils and other contaminants commonly found in the manufacture of medical devices. With excellent materials compatibility it is both safe and easy to use.

Money-saving refills are available from *MicroCare* (photo to the right). These contain the same wipes and fluid as the tubs above, but reduce costs and helps protect the environment by encouraging the re-use of packaging.

AVAILABILITY: Stocked by MicroCare distributors world-wide. Contact MicroCare for a distributor near you. For more information contact MicroCare directly or visit www.MicroCare.com.

MicroCare.com

MicroCare Corporation 595 John Downey Drive

New Britain, CT 06051 USA CAGE: OATV9 Tel: +1 860 827 0626 Toll Free: 1 800 638 0125 Email: TechSupport@MicroCare.com

MicroCare Europe BVBA Vekestraat 29 B11 Industriezone 't Sas 1910 Kampenhout, Belgium Tel: +32 2 251 95 05 Email: EuroSales@MicroCare.com

Technical Details and Cleaning Data	
Boiling Point	82 °C / 180 °F
Chemical Family	Water & Alcohol
Cleaning Strength	25 (est.) (KB value)
Evaporation Rate	Slow
Odor	Slight, Alcohol
Percent Volatile	100%
Specific Gravity	0.87
Health, Safety and Environmental Data	
Flammable	Yes
Flashpoint	12 °C / 53 °F
NFPA	Health: 1 Fire: 3 Instability: 1
Organic Content (g/L)	350
RoHS & WEEE Compliant	Yes
REACH	Yes
US EPA SNAP-Approved	Yes
GHS / HCS Pictogram	
Packaging	
Presaturated Wipes 506 mL fluid content	100 - 5" x 8" Wipes MCC-MLCW
Presaturated Wipe Refills 506 mL fluid content	100 - 5" x 8" Wipes MCC-MLCWR
Recycle	D2 PE-HD

Money-saving refills reduce costs and help protect the environment by reducing waste and encouraging the re-use of packaging.

MicroCare U.K. Ltd

Morley,

LS27 8AT

Seven Hills Business Park,

Leeds, West Yorkshire, UK

Tel: +44 (0) 113 3501008

Email: mcceurope@microcare.com



Follow Us!

MicroCare Asia Pte Ltd

102E Pasir Panjang Road #03-01 Citilink Warehouse Complex Singapore 118529 Tel: +65 6271 0182 Email: TechSupport@MicroCare.sg

Rev. 20142

ISO 9001:2015 Registered

"MicroCare", the MicroCare logo, "MultiClean", "TriggerGrip" and "Discover Perfectly Clean" are trademarks or registered trademarks of MicroCare Corporation. The information set forth herein is based on data believed to be reliable. MicroCare makes no warranties express or implied as to its accuracy and assumes no liability arising out of its use by others. This publication is not to be taken as a license to operate under, nor infringe upon, any patents not herein expressly described.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MicroCare: MCC-MLCW