

CleanBlast™ HFE-Based Cleaning Fluid

Product Features:

- For use with Viavi Solutions® CLEANBLAST fiber end-face cleaning systems
- Cleans dust, lint, oil & grit from fiber end-faces
- High-purity, optic-grade cleaning solvent
- Suitable for use with CLEANBLAST benchtop & portable systems
- Each refill bottle provides 8,000+ cleanings
- Nonflammable
- Leaves no residue

The CLEANBLAST HFE-Based Cleaning Fluid is packaged specifically for use in the VIAVI SOLUTIONS CLEANBLAST fiber end-face cleaning system. This fast drying solvent cleans dust, lint, polishing grit, oil, and fingerprints. Engineered to be a drop-in replacement, this product is VIAVI factory approved for use with the CLEANBLAST cleaning system and uses the same chemistry to ensure compliance with validated manufacturing processes. It is double filtered and packaged to permit the standard spill-resistant CLEANBLAST machine refill process, and contains enough solution for at least 8,000 cleaning cycles per refill. Compatible with all VIAVI CLEANBLAST cleaning tips and suitable for cleaning SC, FC, ST, LC, MU, E2000 and MPO/MTP connectors. Leaves no residue.

Nonflammable and fast evaporating, this cleaning fluid ships as non hazardous/not regulated by all modes of transport, including air freight.

Product Notes

This product is packaged as a direct replacement solvent for use with the following Viavi Solutions CLEANBLAST model numbers:

FCL-P1005	FCL-P1000	FCL-P2000
FCL-P1005-EU	FCL-P1000-EU	

When you need perfectly clean splices & connectors™

www.SticklersCleaners.com



MicroCare Corporation

595 John Downey Drive
New Britain, CT 06051 USA
CAGE: OATV9
Tel: +1 860 827 0626
Toll Free: 1 800 638 0125
Email: TechSupport@MicroCare.com
www.MicroCare.com


MicroCare Europe Bvba

Vekestraat 29 B11
Industriezone 't Sas
1910 Kampenhout, Belgium
Tel: +32 2 251 95 05
Fax: +32 2 400 96 39
Email: EuroSales@MicroCare.com

MicroCare Asia Pte Ltd

102E Pasir Panjang Road
#03-01 Citilink Warehouse Complex
Singapore 118529
Tel: +65 6271 0182
Email: TechSupport@MicroCare.sg



Technical Details	
Odor	Slight, Ether
Boiling Point	45°C/113°F
Chemical family	HFC
Percent Volatile	100
Vapor Pressure @ 20°C	360 mmHG (@25°C)
Non Volatile Residue (% by volume)	<0.010
Health, Safety, and Environmental Data	
Flashpoint	None
Flammable	No
NFPA	Health: 3 Flammability: 1 Instability: 0
Organic Content	889 g/l (@20°C)
RoHS and WEEE Compliant	Yes
GHS/ICS Pictogram	
Packaging	
CLEANBLAST HFE-based Cleaning Fluid 7.61 oz - 225 ml	
Single Bottle Package	#FCLP-SOL1
Six Pack Bottle Package	#FCLP-SOL1-6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MicroCare:

[FCLP-SOL-1](#) [FCLP-SOL1-6](#)