

Sticklers™ MultiTask Surface Cleaner

Presaturated Wipes



Product Features:

- Strong lint-free fabric wipes won't shred, lint or pill—ideal for pre-cleaning
- Removes fingerprints, grime, dust, lint, waterproofing gels, oils and grease from cabinets and equipment in fiber optic and networking environment
- Water and high-purity alcohol for safe cleaning
- Economical cleaning with money-saving refills
- Unique “slam-shut” package for extra long service life
- Unlimited shelf-life

Sticklers™ MultiTask Surface Cleaner presaturated wipes quickly and effectively remove construction dust, fingerprints, grime, metal or plastic particulate, insulation residue, lint, waterproofing gels, oil, grease and some inks.

Disposable fabric wipes provide quick, lint-free cleaning. The wipes are saturated with a mix of high-purity isopropyl alcohol (IPA) and deionized water for versatile cleaning with excellent material compatibility.

Wipes are packaged in a durable, re-usabe, self-closing plastic tub. Each wipe is 5" x 8". Each tub or refill package contains 100 wipes.

AVAILABILITY: Stocked by Sticklers distributors worldwide.

For more information and where to buy, visit SticklersCleaners.com

When you need perfectly clean splices & connectors™

www.SticklersCleaners.com



MicroCare Corporation



595 John Downey Drive
New Britain, CT 06051 USA
CAGE: OATV9
Tel: +1 860 827 0626
Toll Free: 1 800 638 0125
Email: TechSupport@MicroCare.com
www.MicroCare.com

MicroCare Europe Bvba

Vekestraat 29 B11
Industriezone 't Sas
1910 Kampenhout, Belgium
Tel: +32 2 251 95 05
Fax: +32 2 400 96 39
Email: EuroSales@MicroCare.com

MicroCare Asia Pte Ltd

102E Pasir Panjang Road
#03-01 Citilink Warehouse Complex
Singapore 118529
Tel: +65 6271 0182
Email: TechSupport@MicroCare.sg

Technical Details and Cleaning Data	
Boiling Point	82 °C / 180 °F
Chemical Family	Water & Alcohol
Evaporation Rate	Moderate
Odor	Slight, Alcohol
Percent Volatile	100%
Specific Gravity	0.87
Health, Safety and Environmental Data	
Flammable	Yes
Flashpoint	12 °C / 53 °F
NFPA	Health: 1 Fire: 3 Instability: 1
Organic Content (g/L)	350
RoHS and WEEE Compliant	Yes
REACH	Yes*
US EPA SNAP-Approved	Yes
GHS / HCS Pictogram	
Packaging	
Presaturated Wipes 443 mls. fluid content	100 - 5" x 8" Wipes MCC-SMSCW
Presaturated Wipe Refills 443 mls. fluid content	100 - 5" x 8" Wipes MCC-SMSCWR
Recycle	 PE-HD

*Contact Sticklers for specific details

Money-saving refills
reduce costs and help
protect the environment
by reducing waste and
encouraging the re-use
of packaging.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MicroCare:

[MCC-SMSCWR](#) [MCC-SMSCW](#)