

**RoHS Compliant**



**PX-275**

**PCIe 8xRS232 DB25 1MBaud**

**"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"**



#### Description

PCI Express Card providing eight RS232 serial ports connected using 25 pin cables. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows 2000, XP, Server 2003, Vista, Server 2008 and Windows 7.


PCI Express is the latest standard in PC connectivity.

With Brainboxes' industry renowned Lifetime Warranty and Lifetime Support!

#### Features

- 8 port RS232
- PCI Express x1, x4, x8 x16 lane slots socket size
- 32 Byte Tx and 32 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

#### Options




PX-275:  
PCIe 8xRS232 DB25  
1MBaud

#### Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.




#### ORDER

Description

PCIe 8xRS232 DB25 1MBaud






Code

PX-275



# PCIe 8xRS232 DB25 1MBaud

## PX-275: Full Specification

<b>Port</b>  	<b>Port</b>  <b>Connector</b> <b>FIFO size</b> <b>Operating Distance</b> <b>Cable</b>	8 x RS232  DB25 Connector - 25 Pin Male 32 RX FIFO + 32 TX FIFO EIA - RS232 Standard 8 port cable 78 way D to 8x25 Pin Male
<b>Port Settings</b>  	<b>Baud Rate</b>  <b>Data Bits</b> <b>Parity</b> <b>Stop Bits</b> <b>Flow Control</b> <b>Tx/Rx Modes</b>	921,600  5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 RTS/CTS, DSR/DTR, XON/XOFF Point to Point
<b>Interface</b>  	<b>OS Compatibility</b>         <b>BUS</b>	Microsoft Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions Windows Server 2003 32 bit 64 bit Editions Windows XP 32 bit 64 bit Editions  PCI Express x1, x4, x8 x16 lane slots
<b>Approvals</b>	<b>Other Approvals</b>  <b>Microsoft Approvals</b>	AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS METL EMC: CE TAA  Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit editions Windows Vista 32 bit 64 bit editions Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions
<b>General</b>	<b>PCB Layers</b> <b>Power Consumption</b> <b>Weight</b> <b>Size</b>	4 490mA @ 3.3V, 210mA @ 12V awaiting awaiting
<b>Box Content</b>	<b>Packaging</b> <b>Card</b>	Installation CD including manual, Microsoft signed drivers & utilities PCIe 8xRS232 DB25 1MBaud 8 port cable 78 way D to 8x25 Pin Male
<b>Product Support</b>  	<b>Warranty</b> <b>Support</b>	Lifetime (online registration required)  Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
<b>Additional</b>  	<b>OEM option</b> <b>Made In</b> <b>Customisable</b>	Available for bulk buy OEM  Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: <a href="mailto:sales@brainboxes.com">sales@brainboxes.com</a>

Other PCI Express Cards: 1 Port RS232 | 2 Port RS232 | 4 Port RS232 | 8 Port RS232 | 1 Port RS422/485 | 2 Port RS422/485 | 4 Port RS422/485  
Other Brainboxes Ranges: PCI | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial

**+44(0) 151 220 2500 | [sales@brainboxes.com](mailto:sales@brainboxes.com) | [www.brainboxes.com](http://www.brainboxes.com)**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Brainboxes:

PX-275