

The Klein Tools' Fish Tapes are perfect for wire runs associated with short commercial, residential and voice-data-video-audio runs. The high carbon, coated steel is firm with the right amount of flex when pulling wire in attics, down walls, or through small branch circuits.

# 25' WIDE STEEL FISH TAPE



- Durable, high carbon 1/4" wide spring steel fish tapes are firm yet flexible
- New protective coating reduces non-contact moisture and humidity but keeps the steel dry to touch
- Laser etched markings in 1-foot (0.3 m) descending increments allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out
- Slim-profile plastic tip navigates easily and reduces catching
- Polymer case and handle offer the maximum impact resistance
- Compact size makes it a staple for your everyday tool bag

# KLEIN HAS THE RIGHT FISH TAPE FOR YOUR INDUSTRIAL, COMMERCIAL, RESIDENTIAL AND VDV WIRE INSTALLATIONS.



| Cat. No | UPC 0-92644+ | Tape Material           | Tape Length   | End/Leader          | Overall Dimensions                          |
|---------|--------------|-------------------------|---------------|---------------------|---------------------------------------------|
| 56335   | 56335-5      | Spring Steel            | 25-ft (7.6 m) | Plastic Slim Tip    | 1.2" x 7.6" x 8.8" (3.0 x 19.2 x 22.4 cm)   |
| 56331   | 56331-7      | Spring Steel            | 50-ft (15 m)  | Double-Loop         | 1.2" x 7.6" x 8.8" (3.0 x 19.2 x 22.4 cm)   |
| 56002   | 56002-6      | Spring Steel            | 65-ft (20 m)  | Double-Loop         | 1.9" x 9.2" x 12.4" (4.7 x 23.4 x 31.5 cm)  |
| 56333   | 56333-1      | Spring Steel            | 120-ft (37 m) | Double-Loop         | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56334   | 56334-8      | Spring Steel            | 240-ft (73 m) | Double-Loop         | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56340   | 56340-9      | Stainless Steel         | 125-ft (38 m) | Double-Loop         | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56341   | 56341-6      | Stainless Steel         | 240-ft (73 m) | Double-Loop         | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56350   | 56350-8      | Fiberglass              | 50-ft (15 m)  | Spiral Steel Leader | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56351   | 56351-5      | Fiberglass              | 100-ft (30 m) | Spiral Steel Leader | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56380   | 56380-5      | Multi-Groove Fiberglass | 100-ft (30 m) | Spiral Steel Leader | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56382   | 56382-9      | Multi-Groove Fiberglass | 50-ft (15 m)  | Nylon Eyelet        | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |
| 56383   | 56383-6      | Multi-Groove Fiberglass | 100-ft (30 m) | Nylon Eyelet        | 1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm) |

Cat. Nos. 56331, 56333, 56334, 56340, 56341 -- U.S. Pat.: 8164025; 8168921; 8212178; 9895773; 10099316



**PROUDLY MADE IN USA**  
with Global Components



See our complete line of Wire Pulling Tools  
[www.kleintools.com](http://www.kleintools.com)



© 2020 Klein Tools, Inc.  
Lincolnshire, IL 60069  
MKT20200323

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[56335](#)