
RECHARGEABLE 2-COLOR LED **HEADLAMP** and **FLASHLIGHT**

Multi-mode lights for your
everyday lighting needs



800 LUMENS
LÚMENES
LUMENS

1000 LUMENS
LÚMENES
LUMENS

**EACH OFFER
3-LIGHTS-IN-1**

- Focused, long-range white spotlight
- Wide, white floodlight
- Red LEDs

**KLEIN
TOOLS®**



RECHARGEABLE 2 - COLOR LED FLASHLIGHT WITH HOLSTER

56413

MODES

SPOTLIGHT

Boost/High/Low/Strobe



FLOODLIGHT

High/Medium/Eco



RED LED

Solid/Strobe



Equipped with **Last Mode Memory**—turns ON in the same mode as when turned OFF

Collar twists for charging via included USB-C cable




Battery life indicator light:
green/yellow/red

Hold to cycle
from Spotlight /
Floodlight / Red LED

Power button:
Click for Boost /
High / Medium /
Eco / Strobe / Off

Removable
pocket clip

Magnetic end
cap for hands-
free use



Holster can
be mounted to a belt or
backpack



RECHARGEABLE 2 - COLOR LED HEADLAMP

56414

Equipped with
**Last Mode
Memory**—turns
ON in the same
mode as when
turned OFF

Hold to cycle
from Spotlight /
Floodlight /
Red LEDs

Power button:
Click through for
Boost / High /
Medium / Eco /
Strobe / Off modes

**Silicone infused,
adjustable fabric strap**
stays securely on head,
cap or hard hat

Slim profile
pivots up to a 64°

**CONVENIENT MARKER AND
CARPENTER'S PENCIL HOLDER**
(PENCIL/MARKER NOT INCLUDED)

MAGNETIC WORK LIGHT



USB-C charging port
(cable included)



**GREEN/YELLOW/RED
BATTERY GAUGE INDICATES
BATTERY LIFE LEVEL**



**EASILY MOUNTS TO
KLEIN® HARD HATS**



MODES

SPOTLIGHT
Boost/High/Low/Strobe

FLOODLIGHT
High/Medium/Eco

RED LED
Solid/Strobe



RECHARGEABLE 2-COLOR LED HEADLAMP AND FLASHLIGHT

Klein Tools' Rechargeable 2-Color Flashlight and Headlamp both offer multiple light settings and modes fulfilling your everyday lighting needs. Both lights feature a bright, long-reaching white spotlight, a wide white floodlight, low-intensity red LEDs for non-blinding night vision, and a long-lasting red strobe. These smartly designed lights turn back on in the same mode you last turned them off, so fewer clicks to get to your favorite mode. Durable, dustproof, and water-resistant, make these lights must-haves for daily use on, and off, the jobsite.

RECHARGEABLE 2-COLOR LED FLASHLIGHT WITH HOLSTER

56413



FL 1 STANDARD			
Spotlight			
Boost	1000 Lumens	4hr	
High	800 Lumens	7hr	
Low	400 Lumens	11hr	
Strobe	95 Lumens	50hr	
Floodlight			
High	650 Lumens	6hr	
Med	450 Lumens	11hr	
Eco	35 Lumens	25hr	
Red LED			
Solid	4 Lumens	48hr	
Strobe	4 Lumens	96hr	
6 ft		IP64	

RECHARGEABLE 2-COLOR LED HEADLAMP

56414



FL 1 STANDARD			
Spotlight			
Boost	800 Lumens	4hr	
High	600 Lumens	8hr	
Low	300 Lumens	10hr	
Strobe	100 Lumens	40hr	
Floodlight			
High	500 Lumens	5hr	
Med	250 Lumens	10hr	
Eco	30 Lumens	27hr	
Red LED			
Solid	2.5 Lumens	56hr	
Strobe	2.5 Lumens	160hr	
10 ft		IP65	

For Professionals
SINCE 1857™



Cat. No.	UPC 0-92644+	Description	Dimensions
56413	56413-0	Rechargeable 2-Color LED Flashlight with holster	6.3" x 1.4" x 1.3" (16.0 x 3.6 x 3.3 cm)
56414	56414-7	Rechargeable 2-Color LED Headlamp with Fabric Strap	1.65" x 2.88 x 2.2" (4.2 x 7.3 x 5.6 cm)

Visit www.kleintools.com for warnings and instructions.

See our complete line of Illumination
www.kleintools.com



© 2021 Klein Tools, Inc.
Lincolnshire, IL 60069
82946 Rev. 03/21 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[56413](#) [BC520KIT](#)