

HARD HATS

SAFETY • COMFORT • FIT



**KLEIN
TOOLS**



PROTECTION FROM IMPACT, PENETRATION, AND LATERAL DEFORMATION

**KLEIN HARD HATS
ARE TESTED TO THE
LATEST STANDARDS**

TYPE I, CLASS E
ELECTRICAL PROTECTION
UP TO 20KV

TYPE I, CLASS C
ADJUSTABLE SIDE VENTS HELP
MANAGE AIR CIRCULATION

① **ANSI/SEA Z89.1-2014**
CSA Z94.1-15

② **EN12492:2012***:
4.2.1.2, 4.2.1.3, 4.2.1.4,

③ **EN397:2012+A1:2012**:
5.2.4



(Shown:
SKU 60248:
TYPE I, CLASS E)

*This hard hat provides LIMITED protection from small objects striking the top, front, back, left and right sides of the hard hat. This is NOT an ANSI/CSA Type II hard hat.

LONG TERM COMFORT AND OPTIMAL FIT



Pivot Adjustment

allows user to position the ratchet mechanism to clear bandana knots and pony-tails.



Ratchet Adjustment

Large knob mechanism allows for easy one-hand adjustment, even with gloves on.




Replaceable, Top Comfort Pad

Sweat-wicking and breathable padding; machine washable. Prevents straps from digging into your head. (Replacement part # KHHTOPPAD)

Flexible, Open-Frame Design

allows suspension to conform to user's head, provides optimal fit, and improved ventilation.



Rear Neck Pad

Soft, non-slip rear pad provides excellent cushion and grip.

Multi-Point Adjustment

allows user to choose the best position for enhanced fit and comfort.

Chin Strap Attachment Points

Chin Strap is sold separately. (#KHHSTRP)

Replaceable, Sweatband

Front and side coverage; sweat-wicking and breathable padding; machine washable. (Replacement part # KHHSWTBND)

SAFETY • COMFORT • FIT

With a continued focus on optimal safety, comfort and fit, these updated Klein® Hard Hats now offer additional protection from front, back, and side impacts! Long-term comfort and proper fit are achieved with an adjustable, flexible, open-frame suspension that hugs your head for a secure fit, coupled with a padded, sweat-wicking band and replaceable top pad. Vented models add further comfort with large adjustable vents to improve air circulation. All models feature patent pending accessory mounts on the front and back to easily and precisely attach Klein Tools' exclusive Jobsite Headlamps—no straps needed!

CAUTION
HARD HAT
AREA

NON-VENTED **CLASS E**

Specifically built with electricians and linemen in mind, these non-vented hard hats are tested up to 20kV.

Class E, Type 1 hard hat meets
ANSI Z89.1-2014, CSA Z94.1-15,
EN12492:2012**- Front, Back and Side impact
and EN397:2012+A1:2012
-Lateral Deformation
(LD) standards



REVERSE DONNING

Suspension can be easily adjusted to wear hard hat frontwards or backwards



ALL-ON

SPOTLIGHT

FLOODLIGHT



RECHARGEABLE HEADLAMP/MAGNETIC WORKLIGHT #56062

Included on some models and also sold separately, this headlamp has a built-in tab for quick release without removing hard hat. With spot, flood or all-on mode, it tilts and has a built-in magnet to attach to metal surfaces. Also sold separately (#56062)

VENTED **CLASS C**

Built for the demands of general construction, plumbing, carpentry and iron worker use, these hard hats include adjustable vents that can be opened and closed. These hard hats do not provide electrical protection.


Class C, Type 1 hard hat meets
ANSI Z89.1-2014, CSA Z94.1-15,
EN12492:2012**- Front, Back and Side impact and
EN397:2012+A1:2012 -Lateral Deformation (LD) standards

**Select clauses only (See instructions for details)



LARGER VENTS = BETTER VENTILATION

The adjustable vents can be opened or closed for maximum air circulation.



UNIVERSAL ACCESSORY SLOTS

on both sides for hearing protection, face shield, and more.

ACCESSORY MOUNTS

Patent-pending accessory mounts ensure the Klein headlamp is always properly positioned, on **front or back** - with NO STRAP needed!

Rechargeable Headlamp/
Magnetic Worklight
sold separately (#56062)





60100



60107RL



60248



60400



60406RL



60249

NON VENTED CLASS E

Cat. No.	UPC 0-92644+	Class	SKU Description
60100	60076-0	E	Cap style, non-vented, White
60107	60078-4	E	Cap Style, non-vented, Alkaline Headlamp # KHH56220, White (NOT shown)
60107RL	60426-3	E	Cap Style, non-vented, Headlamp #56062, White
60248	60248-1	E	Cap style, non-vented, Blue
60249	60249-8	E	Full brim, non-vented, Blue
60400	60081-4	E	Full brim, non-vented, White
60406RL	60427-0	E	Full brim non-vented, Headlamp #56062, White



60105



60113RL



60401



60407



60407RL



60262

VENTED CLASS C

Cat. No.	UPC 0-92644+	Class	SKU Description
60105	60077-7	C	Cap style, vented, White
60113RL	60425-6	C	Cap Style, vented, Headlamp #56062, White
60401	60082-1	C	Full brim, vented, White
60407	60084-5	C	Full brim, vented, Alkaline Headlamp # KHH56220, White
60407RL	60428-7	C	Full brim, vented, Headlamp #56062, White
60262	60262-7	C	Full brim, vented, Yellow

HEADLAMPS & ACCESSORIES

Cat. No.	UPC 0-92644+	Description	Lumens	Batteries	Battery Life
56062	56062-0	Rechargeable Headlamp/ Magnetic Worklight	Boost: 300 Spot/High: 215 Flood/Low: 100	Rechargeable, Lithium-ion	Boost: 4 hrs Spot/High: 9 hrs Flood/Low: 14 hrs
56048	56048-4	Rechargeable Auto-Off Headlamp	Boost: 400 Spot/High: 200 Flood/Low: 100	Rechargeable, Lithium-ion	Boost: 4 hrs Spot/High: 12 hrs Flood/Low: 22 hrs
56049	56049-1	Rechargeable Light Array Headlamp/ Magnetic Worklight	High: 260 Low: 125	Rechargeable, Lithium-ion	High: 9 hrs Low: 14 hrs
KHH56220	56043-9	Alkaline Headlamp/ Magnetic Worklight	Spotlight: 150 Floodlight: 50	3 x AAA	Spotlight: 6 hrs Floodlight: 10 hrs

Cat. No.	UPC 0-92644+	Description	Pkg Qty
KHHSPN	60087-6	Klein Tools Hard Hat Replacement Suspension	1
KHHTOPPAD	60088-3	Klein Tools Hard Hat Replacement Top Pads	3
KHHSWTBND	60089-0	Klein Tools Hard Hat Replacement Sweatbands	3
KHHSTRP	60119-4	Klein Tools Hard Hat Chin Strap	1



KHHSPN



KHHSTRP



KHHTOPPAD



KHHSWTBND

For Professionals
SINCE 1857™

Warning statement: Visit www.kleintools.com for safety warnings.



See our complete line of **Personal Protective Equipment**
www.kleintools.com



© 2020 Klein Tools, Inc.
Lincolnshire, IL 60069
82810 Rev. 07/20 B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[60249](#) [60113RL](#) [60406RL](#) [60262](#) [60248](#) [60107RL](#) [60407RL](#)