

# VOLTAGE

# TESTERS

## ET60

Electronic AC/DC  
Voltage Tester



600V  $\sim$

LOW  
Z

## ET250

Digital AC/DC Voltage  
and Continuity Tester



600V  $\sim$

GFCI



**KLEIN  
TOOLS**   
For Professionals... Since 1857™




TOUGH METER VOLTAGE TESTERS



ET60  
Electronic AC/DC  
Voltage Tester

ET60 is a solid-state, low impedance, electronic voltage tester. It measures AC/DC voltages up to 600V. The ET60 does NOT require batteries; it is powered by the applied voltage. It is an excellent choice for testing voltage in electrical circuits, at outlets, in light fixtures or anywhere else where AC/DC voltage testing is required.

- Modern solid-state design
- Does NOT use a battery
- Low impedance
- Integrated test-lead holders (on back)
- **TOUGH METER** design is water and dust resistant and withstands 9.8 ft. (3m) drops



Voltage indicator lights up to voltage amount. DC Polarity Indicators (indicates AC when both are illuminated).



Test-leads seated in the lead holders on the back of the tester are spaced correctly to test tamper-resistant US-style outlets.



ET60	FEATURES	ET250
9.8 ft. (3m)	Drop Protection	9.8 ft. (3m)
IP54	Ingress Protection	IP53
CAT IV 600V	Safety	CAT IV 600V
600V	AC Voltage (Volts)	600V
600V	DC Voltage (Volts)	600V
—	Audible Continuity	•
—	Backlight	•
•	Low Impedance	—
•	GFCI-Protected Circuit Testing	•
—	Flashlight	•
—	Auto-Power Off	•
Not Required	Battery	3 x AAA
—	LCD Display with Backlight	•

Cat. No.	UPC# 0-92644+	Batteries	Height	Width	Depth	Weight (oz.)
ET60	69036-5	Not required	5.67" (144 mm)	2.35" (59.7 mm)	1.44" (36.6 mm)	3.2 (92 g)
ET250	69037-2	3 x AAA	6.06" (153.8 mm)	2.33" (59.2 mm)	1.64" (41.6 mm)	6.0 (170 g)

\*Set of Klein test-leads included in package



Voltage Indicator LEDs

DC Polarity Indicators (indicates AC when both are illuminated)

BOTH MODELS  
WORK WITH MOST  
STANDARD REPLACEABLE  
TEST-LEADS\*

Test-lead input jacks

LCD Display with Backlight

Power On/Off

Worklight Backlight

GFCI Test Button



Integrated Flashlight

ET250  
Digital AC/DC Voltage  
and Continuity Tester

ET250 is a solid-state, digital voltage and continuity tester. It measures AC/DC voltages up to 600V and tests for continuity. Additionally, the ET250 tests GFCI protected circuits to verify that the GFCI device is functioning appropriately. The tester includes a backlight and integrated flashlight for working in reduced ambient lighting conditions.

- Automatically selects measurement mode
- Auto-powers on when a voltage/continuity measurement is attempted
- Modern solid-state design
- Tests GFCI protected circuits
- Built-in test lead holders
- Backlit LCD display
- Integrated flashlight
- **TOUGH METER** design is water and dust resistant and withstands 9.8 ft. (3m) drops



Flashlight and backlit display when working in zero to low light situations. LCD screen provides more accurate voltage measurement.



Tests GFCI protected circuits



TOUGH METER VOLTAGE TESTERS



***Tested Tough.***  
***Trust Klein.***



See our complete line of Test & Measurement products at  
**[www.kleintools.com](http://www.kleintools.com)**

**KLEIN TOOLS**  
EST. 1857  
For Professionals... Since 1857™



© 2017 Klein Tools, Inc.  
Lincolnshire, IL 60069-1418  
96486 Rev. 03/17 A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[ET60](#) [ET250](#)