

# Hi-Visibility Tools

Don't Let Your Klein® tools

## DISAPPEAR!



**ADDITIONAL  
PLIERS NOW  
AVAILABLE!**

**KLEIN  
TOOLS®**



For Professionals... Since 1857® USA



# Grips Glow in the Dark

## to help find your tools.


Lasts up to 30 minutes!\*

### Grips charge

in natural and artificial lighting.

### Glow in the dark grips

to easily locate your tool in dark or low lit areas.



**SIDE-CUTTING PLIERS  
HIGH-LEVERAGE**

**D2000-9NEGLW**

- Cuts ACSR, screws, nails, and most hardened wire.
- High-leverage design.
- Sure-gripping cross-hatched knurled jaws.



**DIAGONAL-CUTTING PLIERS  
HIGH-LEVERAGE**

**D2000-28GLW**


- Cuts ACSR, screws, nails, and most hardened wire.
- High-leverage design.
- Short jaws and beveled cutting edges permit close cutting of wire, nails, and most hardened wire.



**WIRE STRIPPER/CUTTER**

**11054GLW**

- Cuts, strips and loops 8-16 AWG Solid and 10-18 AWG Stranded wire.
- Strong-gripping serrated nose for easy bending, shaping, and pulling of wire.
- Shears 6-32 and 8-32 screws.



**DIAGONAL-CUTTING PLIERS  
ANGLED HEAD HIGH-LEVERAGE**

**D248-8GLW**

- Angled head design for easy work in confined spaces.
- Short jaws and beveled cutting edges permit close cutting of wire, nails, and most hardened wire.
- High-leverage design.



**LONG-NOSE PLIERS  
HEAVY DUTY SIDE-CUTTING**

**D203-8GLW**

- Slim head design for easy work in confined spaces.
- Heavier design for greater cutting power.
- Extended handles provide added reach and leverage.

Cat. No.	UPC# 0-92644+	Overall Length	Strips and Cuts	Jaw Length	Jaw Width	Jaw Thickness	Handle Finish	Weight (lbs.)
D2000-9NEGLW	38003-7	9-3/8" (238 mm)	N/A	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	hi-visibility	1.09
D2000-28GLW	38004-4	8-1/16" (205 mm)	N/A	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	hi-visibility	.67
11054GLW	34115-1	7-1/8" (181 mm)	8 - 16 AWG solid (8.4 mm <sup>2</sup> - 1.3 mm <sup>2</sup> ) & 10 - 18 AWG stranded (5.3 mm <sup>2</sup> - .82 mm <sup>2</sup> )	N/A	N/A	N/A	hi-visibility	.34
D248-8GLW	72022-2	8-1/16" (205 mm)	N/A	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	hi-visibility	.60
D203-8GLW	71004-9	8-7/16" (214 mm)	N/A	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	hi-visibility	.60

## Two interactive displays available

Cat. No.	Description	Qty. 4 of Each
96356	12 pc. Interactive Counter Display	D2000-9NEGLW, D2000-28GLW and 11054GLW
96256	12 pc. Interactive Counter Display	D248-8GLW, D203-8GLW and 11054GLW



**KLEIN TOOLS**

For Professionals... Since 1857® USA

[www.kleintools.com](http://www.kleintools.com)



© 2014 Klein Tools, Inc.  
Lincolnshire, IL 60069-1418  
Rev. 06/14 96350

Hi-Visibility Tools

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[D248-8-GLW](#) [D203-8-GLW](#)