

Utility Hand Tools

Klein® manufactures the highest quality tools in the industry, supporting linemen and utility workers around the world with premium products—quality and reliability you can count on every day.



**KLEIN
TOOLS®** 
For Professionals... Since 1857®

Open Jaw Cable Cutter

- High-leverage ratchet mechanism for single-handed cutting of copper and aluminum without burrs or sharp edges.
- Front loading jaws for tight applications.
- Spring release lever allows for fast jaw reset in between cuts.
- Plastic covered handles with hand guards for comfort and firm grip.
- One-year warranty.

| Cat. No. | Max. Cable Cutting Capacity | Overall Length | Weight |
|----------|--|------------------|--------------------|
| 63711 | 600 MCM (300 mm ²) Copper and 750 MCM (400 mm ²) Aluminum 1-1/8" Communication cable | 11.5" (292.1 mm) | 2.0 lbs. (0.91 kg) |

⚠WARNING: Do NOT use to cut steel or ACSR.

Capacity



63711

3-in-1 Impact Socket – Distribution | Transmission

- NRHD Distribution socket features three square socket sizes: 3/4", 1", and 1-1/8".
- NRHD2 Transmission socket features three square socket sizes: 1-1/8", 1-5/16", and 1-1/2".
- 7/16" hex quick-change adapter included.
- Fine-tuned ball detent provides improved retention, minimizing drops.
- Long hollow shaft allows use on long threaded bolts.

| Cat. No. | Overall Length | Weight |
|----------|-------------------|---------------------|
| NRHD | 7 3/4" (196.9 mm) | 2.0 lbs. (0.91 kg) |
| NRHD2 | 11" (279.4 mm) | 3.25 lbs. (1.47 kg) |



NRHDA



NRHDA2

Impact Socket Adapters

- Impact socket adapter.
- 7/16" hex quick-change adapter.
- Fine-tuned ball detent provides improved retention, minimizing drops.
- Do not exceed 200 ft. lbs of torque.

| Cat. No. | Description | Hex Size |
|----------|-----------------------------|----------|
| NRHDA | Distribution Socket Adapter | 7/16" |
| NRHDA2 | Transmission Socket Adapter | 7/16" |

NRHD



NRHD2



Klein-Kurve® Skinning Knife

- 2" blade for increased control when scoring and slitting cable jacket.
- Ergonomic handle for maximum comfort.
- Oversized ring for strength and easy storage.
- Notch on blade back for scraping or removing wire insulation.



1580-3

| Cat. No. | Overall Length | Weight |
|----------|-------------------|---------------------|
| 1580-3 | 8-3/4" (222.3 mm) | 0.28 lbs. (0.13 kg) |



25" Standard Cable Cutter

- Replaceable hook-jaw blades grab and hold cable while shear-cutting action makes clean cuts.
- Fiberglass handles with heavy vinyl grips for comfort and slip resistance.
- Jaws are forged tool steel with black-oxide finish for long life.
- Minimal blade friction allows handle to be opened using only gravity.
- Make a clean, even cut for ease in fitting lugs and terminals.
- Not designed for cutting steel or ACSR.
- Includes rubber sleeves.



Rollpin prevents snags



63041TH

| Cat. No. | Soft Cable Capacity | MCM Cable Capacity | Overall Length | Weight |
|----------|---------------------|------------------------------|----------------------|------------------------|
| 63041TH | 1-3/8" (35 mm) | Copper: 500 Aluminum: 750 | 25 -1/2" (648 mm) | 5.25 lbs. (2.38 kg) |

▲WARNING: Do NOT use to cut steel or ACSR.



Pole Punch

- Ergonomic handle with overstrike protection.
- Thermoplastic handle withstands harsh conditions and is resistant to oil and grease.
- Large strike plate transfers force directly into the hardware, reducing vibration.
- Chamfered tip assists centering and reduces drag.



66326

| Cat. No. | Overall Length | Weight |
|----------|----------------|---------------------|
| 66326 | 18" (457.2 mm) | 1.03 lbs. (0.47 kg) |



KLEIN TOOLS
For Professionals... Since 1857®

See our complete line of Utility Hand Tools at

www.kleintools.com



© 2013 Klein Tools, Inc.
Lincolnshire, IL 60069-96833
Printed in U.S.A. 96349



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[1580-3](#) [NRHDA3](#)