


Accessories

Auxiliary contact


Front mount blocks

Side mount blocks


Screw clamp connection




Fast-on connection



Cage clamp connection



Solder pin connection





Catalog No.

Connection type	Applying contactors	Mounting type	Composition	Catalog no.
Screw clamp	CGMS-, CGMSS-, CGMUS- 6A(D) 9A(D) 12A(D) 16A(D)	Front mount	2NO	AX-2MS20
			2NC	AX-2MS02
			1NO+1NC	AX-2MS11
			4NO	AX-4MS40
			3NO+1NC	AX-4MS31
			2NO+2NC	AX-4MS22
			1NO+3NC	AX-4MS13
			4NC	AX-4MS04
		Side mount	1NO	AX-1MS10
			1NC	AX-1MS01
Fast-on	CGMF-, CGMSF-, CGMUF- 6A(D) 9A(D) 12A(D) 16A(D)	Front mount	2NO	AX-2MF20
			2NC	AX-2MF02
			1NO+1NC	AX-2MF11
			4NO	AX-4MF40
			3NO+1NC	AX-4MF31
			2NO+2NC	AX-4MF22
			1NO+3NC	AX-4MF13
			4NC	AX-4MF04
		Side mount	1NO	AX-1MF10
			1NC	AX-1MF01
Cage clamp	CGMC-, CGMSC-, CGMUC- 6A(D) 9A(D) 12A(D) 16A(D)	Front mount	2NO	AX-2MC20
			2NC	AX-2MC02
			1NO+1NC	AX-2MC11
			4NO	AX-4MC40
			3NO+1NC	AX-4MC31
			2NO+2NC	AX-4MC22
			1NO+3NC	AX-4MC13
			4NC	AX-4MC04
		Side mount	1NO	AX-1MC10
			1NC	AX-1MC01
Solder pin	CGMP-, CGMSP-, CGMUP- 6A(D) 9A(D) 12A(D) 16A(D)	Side mount	1NO	AX-1MP10
			1NC	AX-1MP01

CGMS-12A

+

AX-4MS





0.21kg

CGMS-12D


+

2 × AX-1MS




0.21kg

AX-4MS




0.04kg

AX-2MS



0.03kg

AX-1MS



0.02kg

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Carlo Gavazzi:

[AX-1MF-10](#) [AX-4MF-13](#) [AX-1MP-01](#) [AX-1MS-01](#) [AX-1MS-10](#) [AX-4MS-13](#) [AX-4MS-22](#) [AX-4MS-31](#) [AX-1MP-10](#)
[AX-4MS-04](#) [AX-2MF-20](#) [AX-2MS-11](#) [AX-2MS-02](#) [AX-2MS-20](#) [AX-1MF-01](#) [AX-2MC-20](#) [AX-2MF-11](#) [AX-4MF-40](#)
[AX-1MC-01](#) [AX-2MC-11](#) [AX-2MF-02](#) [AX-4MF-31](#) [AX-4MF-04](#) [AX-4MF-22](#) [AX-4MS-40](#)