





# APEX™ 150



Sealed Connection Systems

## FCI 14 Way APEX 150 Hybrid Connection System

**FEMALE**



**MALE**



| INDEX TYPE | HOUSING COLOR | PLUGGED SEAL POSITIONS (X) |   |   |   |   |   |   |   |   |    |    |    |    |    | FEMALE ASSEMBLY PART NUMBER | MALE ASSEMBLY PART NUMBER (SLOT 1) | MALE ASSEMBLY PART NUMBER (SLOT 2) |
|------------|---------------|----------------------------|---|---|---|---|---|---|---|---|----|----|----|----|----|-----------------------------|------------------------------------|------------------------------------|
|            |               | 1                          | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 |                             |                                    |                                    |
| A          | BLACK         |                            |   |   |   |   |   |   |   |   |    |    |    |    |    | 55251400                    | 54251400                           | 54251404                           |
| B          | GREY          |                            |   |   |   |   |   |   |   |   |    |    |    |    |    | 55251401                    | 54251401                           | 54251405                           |
| C          | BROWN         |                            |   |   |   |   |   |   |   |   |    |    |    |    |    | 55251402                    | 54251402                           | 54251406                           |
| D          | GREEN         |                            |   |   |   |   |   |   |   |   |    |    |    |    |    | 55251403                    | 54251403                           | 54251407                           |
| A          | BLACK         | X                          |   |   |   |   |   |   |   |   |    |    |    |    | X  | 55251408                    | 54251412                           |                                    |
| B          | GREY          | X                          |   |   |   |   |   |   |   |   |    |    |    |    | X  | 55251409                    | 54251413                           |                                    |
| A          | BLACK         |                            |   |   |   |   | X |   |   |   |    |    |    |    |    | 55251410                    | 54251416                           | 54251418                           |
| B          | GREY          |                            |   |   |   |   | X |   |   |   |    |    |    |    |    | 55251411                    | 54251417                           | 54251419                           |
| A          | BLACK         | X                          |   |   |   |   | X |   |   |   |    |    |    |    |    | 55251412                    | 54251420                           | 54251422                           |
| B          | GREY          | X                          |   |   |   |   | X |   |   |   |    |    |    |    |    | 55251413                    | 54251421                           | 54251423                           |
| A          | BLACK         | X                          |   |   |   |   | X |   |   |   |    |    |    |    | X  | 55251414                    | 54251424                           | 54251426                           |
| B          | GREY          | X                          |   |   |   |   | X |   |   |   |    |    |    |    | X  | 55251415                    | 54251425                           | 54251427                           |
| A          | BLACK         | X                          |   |   |   |   | X |   |   | X |    |    |    |    | X  | 55251416                    | 54251428                           | 54251430                           |
| B          | GREY          | X                          |   |   |   |   | X |   |   | X |    |    |    |    | X  | 55251417                    | 54251429                           | 54251431                           |
| E          | YELLOW        |                            | * | * |   |   |   |   |   |   |    |    |    |    |    | 55251404                    |                                    | 54251408                           |
| F          | YELLOW        |                            |   |   | * | * |   |   |   |   |    |    |    | *  | *  | 55251405                    |                                    | 54251409                           |
| G          | YELLOW        |                            | * | * |   |   |   |   |   |   |    |    |    |    |    | 55251406                    |                                    | 54251410                           |
| H          | YELLOW        |                            |   |   | * | * |   |   |   |   |    |    |    | *  | *  | 55251407                    |                                    | 54251411                           |

NOTE 1: Assembly part numbers also available without CPA. See sale drawing for part numbers

NOTE 2: See Page 8 for explanation of clip slot type 1 and clip slot type 2.

\* Shorting bar exists in this position.

Additional plugged cavity configurations are available upon request.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[54251401](#) [55251401](#) [54251412](#) [54261400](#) [55251406](#) [55251408N](#) [55251409](#) [55261400](#) [55251401-B](#) [54251400-B](#)  
[54251416](#) [54251400](#) [55251400](#) [55251400N](#) [55251401N](#) [55251402N](#) [55251403N](#) [55251402](#) [55251402-B](#)  
[54251401-B](#) [54251412-B](#) [55251402N-B](#) [55251409-B](#) [55251400N-B](#) [55251403N-B](#) [54261400-B](#) [55251401N-B](#)  
[55251408N-B](#) [55261400-B](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[55251400-B](#)