


1. REFERENCES

- TEMPERATURE CLASS 3 (-40° C TO 125° C)
VIBRATION CLASS 1 (ON BODY OR CLASS 5)
SEALING CLASS 2 OR 3 (SEALED - CONNECTOR & CABLE SEAL DEPENDENT)
- B. REFERENCE MATING COMPONENTS OR EQUIVALENTS:
- TERMINAL 13919132
9. TYPICAL CABLE SEAL PART NUMBER IS A REFERENCE FOR A DELPHI CABLE SEAL THAT ACCEPTS CABLE SIZES SIMILAR TO THE CORRESPONDING TERMINAL AND MATES TO THE SAME CONNECTOR CAVITY. CABLE DIAMETER DESIGNATED FOR APPLICATION NEEDS TO BE WITHIN ALLOWABLE RANGE SHOWN ON CABLE SEAL DRAWING



1		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART	
FROM	0		
TO	12	> 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
+0.1		+0.2	
ANGLE & TOLERANCE ±2°			

• APTIV •									
CONNECTION SYSTEMS									
KORLEN, D.									
COPYRIGHT 1974 BY APTIV. ALL RIGHTS RESERVED.									
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV PATENTED INFORMATION. REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED DATA CARDS, AS WELL AS COMMUNICATION OF ANY INFORMATION TO OTHERS WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
								DATE	
R									B
DRI	ALAIN PREVOST							2BMA14	
DRI	ALAIN VIGIER							2BMA14	
DRI	RAYMOND J. BLASKO							2BMA14	
DES									
DES									
SUBSTANCES, FOR CONCENTRATES AND RECYCLED CONTENT FROM APTIV (FORWASH)									
LITERATURE									
DRAWING NAME									
TAXI TERM M OCS 1.5 SEALED									
DRAWING NUMBER									
1 3954065									
A									
SIZE	SHEET	OF	TITLE	OF	REV	NOF			
1/32	10:1	1	O F I	O F I	R	O S	-		

13620423

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13964786](#)