









E CLASSIFICATION ACC.	LV 214	USCAR-2 Rev.6
SEALING CLASSIFICATION	IPX9K	S2 Seq. T, U, W, AC
VIBRATION CLASSIFICATION SEVERITY	SEVERITY 2	V2
TEMPERATURE RANGE	-40...+105° C	T2
THE PRODUCT SPECIFICATION IS BINDING		
*ONLY WITH PROTECTION COVER		



DIMENSION TABLE		6	CPA	>PBT-GF20<		RED	3001		
		5	REAR GRID	>PBT-GF15<		NATURAL	-		
		4	MAT SEAL	>VMQ<; 20 SHORE A		REDDISH BROWN	3013		
		3	HOUSING SEAL	>VMQ<; 50 SHORE A		REDDISH BROWN	3011		
NUMBER OF CAVITY	a	b	c	2	SECONDARY LOCK	>PBT-GF30<	VIOLET	4006	
4 WAY	13.1	2.95	2.25	1	ASM HOUSING	>PBT-GF15<	BLACK	9011	
6 WAY	14.9	3.85	3.15			CAVITY MODULE	>PBT-GF20<	SEE TABLE	
8 WAY	16.7	4.75	4.05		MATERIAL			COLOUR	SIMILAR RAL
10 WAY	18.5	5.65	4.95		ITEM	DESIGNATION			
12 WAY	20.3	6.55	5.85						

AVAILABLE MULTI-WAY FEMALE CONNECTORS								COMPOSITION FEMALE CONNECTOR															
APTIV NUMBER								ASM, HOUSING															
								CODING										SECONDARY LOCK	HOUSING SEAL	MAT SEAL	REAR GRID	CPA	
8 WAY (SERIAL)	8WAY (PRE-SERIAL)	WEIGHT CONNECTOR (g)	10 WAY	WEIGHT CONNECTOR (g)	12 WAY	WEIGHT CONNECTOR (g)	COLOUR OF CAVITY MODULE	SIMILAR TO RAL	A	B	C	D	E	F	G	H	J						
35364118	35398719	3.73	--	--	--	--	BLACK	9011	X										X	X	X	X	X
35374049	35398720		--	--	--	--	WHITE	9010		X													
35374050	35398722		--	--	--	--	BLUE	5012			X												
--	--		--	--	--	--	VIOLET	4004				X											
--	--		--	--	--	--	GREEN	6017					X										
--	--		--	--	--	--	BROWN	8011						X									
--	--		--	--	--	--	GREY	7036								X							
--	--		--	--	--	--	LIGHT PINK	3015									X						
--	--		--	--	--	--	BEIGE	1001										X					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35371049](#)