PORTE-CLIPS *FEMALE CONNECTOR*	211 PC 02 2S 0 010	PBT NON CHARGE *PBT NO LOADED*	NOIR / *BLACK*		
CONTACT *FEMALE TERMINAL*	SICMA	Cu Mg I ou Cu Fe 2P	1.5 x 0.8	I	PRE-ETAME *PRE-TINNED*
DESIGNATION	REF FCI	MATIERE *RAW MATERIAL*	COULEUR / TYPE *COLOR /TYPE*	GAMME *RANGE*	REVETEMENT *PLATED*

DRAWING NUMBER *NUMERO DU PLAN*	211 FT 0439	REVISION *INDICE*	D04	SHEET *FEUILLE* 1/1
DRAWING *PLAN*	-	APPROVAL LEVEL *NIV. D'APPROBATION*		-



ECHELLE 1:1
SCALE 1:1



COUPE E-E







REPERE D'ALVEOLE VOIE 1
IDENTIFICATION OF CAVITY FOR CONTACT WAY 1

ZONE DE MARQUAGE MATIERE
MATERIAL IDENTIFICATION AREA





SECTION H-H

ECHELLE : 5/2
SCALE : 5/2

TOLERANCES : ±0.1

NOIR / *BLACK*	MARRON / *BROWN*	VERT / *GREEN*	BLEU / *BLUE*	CRYSTAL / *WHITE*	COULEUR *COLOR*	INDICE *REVISION* PLAN *DRAW.*	INDICE *REVISION* PIECE *PART*
211 PC 02 2S 0 010	211 PC 02 2S 1 010	211 PC 02 2S 5 010	211 PC 02 2S 6 010	211 PC 02 2S 9 010	REF FCI	D05	D

NOTA :
CODAGE NOIR REPRESENTE
REPRESENTED BLACK CODING

ARCHIVE LE09/04/2004

ECN-NO. *NUMERO ECR*	DATE *DAT MM / YY*	REVISION *INDICE*	POSITION *POSITION*	CHANGE DESCRIPTION *MODIFICATION*	DRAWN BY *DESSINE PAR*	CHECKED BY *VERIFIE PAR*	APPROVED BY *APPROUVE PAR*
A 04 015	05/04/04	D04	-	INCREASED FLAT LENGTH AND MOVED HINGE	F.FAURIE		ANONYME
			-	LOCATION - MARKING CHANGED			
			-	-			
			-	-			

PRODUCT SPEC. *SPECIF. PRODUIT* -	PACKAGING SPEC. *SPECIF. EMBALLAGE* -	APPLICATION SPEC. *SPECIF. APPLICATION* -	THIS DRAWING AND ALL OTHER INFORMATION CONTAINED THEREIN IS PROPRIETARY AND THE PROPERTY OF FCI. This drawing may not be copied, reproduced or disclosed to any third party without the expressed written permission of FCI. © FCI April 1999	CE PLAN ET LES INFORMATIONS CONTENUES DANS CE PLAN SONT PROPRIETAIRES ET LA PROPRIETE DE FCI. Ce plan ne peut être copié, reproduit ou transmis sans l'autorisation expresse et écrite de FCI. © FCI Avril 1999	

TOLERANCES *TOLERANCES*	±0.2 ±2°	MATERIAL : *MATIERE :*	SEE TABLE	SURFACE FINISH *ETAT DE SURFACE*	-
CONTEXPART N° *CONTREPARTIE N°*	--	COLOUR : *COULEUR :*	--		--
DO NOT SCALE DRAWING *NE PAS PRENDRE DE COTES*		TOOL NO. *OUTIL N°*		ECO Loc. Code *CODE B.E.*	FE

DRAWN BY *DESS. PAR*	DATE *DATE* 29/01/03	NAME *NOM* F.FAURIE	TITLE *DESIGNATION*	2 WAY FEMALE TERMINAL	DRAWING NUMBER *REFERENCE PLAN* 211 FT 0439
CHECKED BY *VERIF. PAR*					
APPROVED BY *APPR. PAR*			ESP NO. *NUMERO ESP.* FRA-0479	CAT. NO. *NUMERO CAT.* --	FILE NAME *NOM DE FICHIER* 211FT0439

ISO PROJECTION *PROJECTION ISO* | DIMENSION IN MILLIMETERS *DIMENSIONS EN MILLIMETRES* | CAD SYSTEM pro / engr. | DWG SIZE *FORMAT* A1 | SHEET *FEUILLE* 1 of 1 *sur* 1 | SCALE *ECH* 4:1

EUR P10 16 F28

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aptiv:
10738111