













ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33341413	01	CODE A	ALL PARTS VO / 19,9
33341414	01	CODE B	
33341415	01	CODE C	
33341416	01	CODE D	
33347532	01	CODE A	ALL PARTS NVO / 19,3
33347533	01	CODE B	
33347535	01	CODE C	
33347537	01	CODE D	

	7				6				5				4		3
POSITION	1									2		3			
NAME	HOUSING STRAP MOUNT									SECONDARY LOCK		SL SEAL			
MATERIAL	PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE				
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN				
PART-NO.:	33338832	33338834	33338836	33338838	33347311	33347317	33347320	33347323	33338898	33344860	33283927				
-	---	---	---	---	---	---	---	---	---	---	---	---			
-	1	---	---	---	---	---	---	---	1	---	1				
-	---	1	---	---	---	---	---	---	1	---	1				
-	---	---	1	---	---	---	---	---	1	---	1				
-	---	---	---	1	---	---	---	---	1	---	1				
-	---	---	---	---	1	---	---	---	---	1	1				
-	---	---	---	---	---	1	---	---	---	1	1				
-	---	---	---	---	---	---	1	---	---	1	1				
-	---	---	---	---	---	---	---	1	---	1	1				




NOTES	
-	ON MAIN VIEW ASSEMBLY 33341413 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269104-CUS71 - PRELIMINARY ASSEMBLY 35269104-CUS72 - HARNESS ASSEMBLY 35269103-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 8 WAY 1.5 FEMALE CONNECTOR ASM DWG-NO.: 35153960 - BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CS6) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CS6) - PROTECTION CAP APTIV DWG-NO.: 35428682 (HT DWG-NO.: 17-2271-001-CS6)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 MAX WIRE CROSS SECTION: 1.0MM ² RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM ² - USE COMBINATION: TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK
8	INTERFACE FOR CLIP MOUNTING HT CLIP NUMBER: YCCSFT6.5PT0.8-2.5; FT6LG.M.St.Aufn.II

DIMENSIONAL RANGE (MM)		CHART E1								
☐ DIM TO CHECK	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
	TO	20	30	70	100	150	200	250	300	400
☐ DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED									
		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
☐ THEORETIC DIM	ANGULAR TOLERANCE ±2°									

3					2					1				
DWG STATUS					ZONE	REVISION HISTORY					AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P/CHG											
19NO18	R	01				INITIAL RELEASE						P.BAL	P.NAJ	M.GRU
29MR19	R	01	AA	B7 A7		REFERENCE HELLERMANN TYTON DWG-NO. ADDED CLIP REFERENCE CHANGED						K.FAR	M.GRU	K.PIT
27OC20	R	01	AB	B7 69 B7		PROTECTION CAP APTIV DWG-NO.: 35428682 WAS 35274876 PART AVAILABILITY FOR PART NUMBERS 33347532, 33347533, 33347535, 33347537 UPDATED NOTES UPDATED						P.NAJ	M.GRU	

SCALE
1:1



• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE POWELANE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEJKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAŻNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	P.BALAJI	DATE	18NO18
APVD1	P.NAJDUCH		19NO18
APVD2	M.GRUDZEWSK		20NO18
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001

MATERIAL
SEE CHART

DRAWING NAME
8 WAY 1.5
CTCS STRAP MOUNT MALE ASSEMBLY

DRAWING NUMBER
35153957

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33341413](#)