



DRAWING NUMBER					
15326973					
SIZE	SCALE	FRAME NO	SHEET NO	STG	RE
A1x3	5:1	2 OF 2	1 OF 2	R	3

33132249	-	01	-	224	33132249	15326866 / 14062624	15326865 / 14062642
33132238	-	01	-	223	33132237	15326852	15326851
33132226	-	01	-	221	33132225	15326859	15326858
13969755	-	01	-	222	13961707	15326866	15326865
13969754	-	01	-	220	13961706	15326866	15326865
13969753	-	01	-	219	13961705	15326866	15326865
13969752	-	01	-	218	13961704	15326866	15326865
13969751	-	01	-	217	13961703	15326866	15326865
13544615	-	01	AC	214	13544614	15326859	15326858
15455282	-	01	AD	210	15455281	15326845	15326844
15463280	-	01	AD	205	15463279	15326837	15326836
1545638	-	02	05	1545635	15326838 / 14062616	15326837 / 14062617	
1530777	-	01	AE	212	1530636	15326852	15326851
15479300	-	01	AF	116	15479299	15326866 / 14062641	15326865 / 14062642
15465947	-	02	AD	128	15465025	15326852 / 14062628	15326851 / 14062629
15465946	-	02	AF	124	15465024	15326851 / 14062628	15326850 / 14062629
15465945	-	02	AH	106	15465021	15326838 / 14062616	15326837 / 14062617
15465944	-	02	AF	104	15465020	15326838 / 14062616	15326837 / 14062617
15326863	406245	02	AH	116	15326862 / 14062644	15326866 / 14062641	15326865 / 14062642
15326866	406238	02	AK	114	15326855 / 14062637	15326859 / 14062634	15326858 / 14062635
15326862	406231	02	AK	112	15326849 / 14062630	15326851 / 14062628	15326850 / 14062629
15326842	406225	02	AK	110	15326841 / 14062622	15326845 / 14062622	15326844 / 14062623
15326835	406219	02	AK	108	15326834 / 14062618	15326838 / 14062616	15326837 / 14062617
PART NO	ID	REV	N/P	TYPE	CONNECTOR	CONNECTOR SEAL	PLR

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION  
[USE MATH MODEL FOR PRECISE DIMENSIONS]. FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED TO BUILD  
BUILD, USE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR  
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR  
VARIATIONS, GROUNDING FLAKES, AND OTHER DEFECTS DO NOT AFFECT THE  
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DNP4-4.7-CS-C
3. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
4. THIS CONNECTION MEETS OR EXCEEDS SAE/USCAR-2 AUGUST 1997,  
SECTION 5.3.1.2. TERMINAL DISENGAGE CRITERIA WITH THE APPLICATION  
OF A TERMINAL POSITION ASSURANCE (TPA) SECONDARY LOCK.

DIMENSIONAL RANGE (MM)		LIMITS ARE ESTABLISHED									
FROM	TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400	CHART
TOLERANCE UNLESS OTHERWISE SPECIFIED											
		+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2	

[illegible]

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)  
[15326863](#)